

Eaton 102689

Catalog Number: 102689

Eaton Moeller series NZM - Molded Case Circuit Breaker. Molded Case Switch, 3p, 800A



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM molded case switch	102689
	EAN
	4015081025497
Product Length/Depth	Product Height
401 mm	207 mm
Product Width	Product Weight
210 mm	21 kg
Compliances	Certifications
RoHS conform	Specially designed for North America
	CE marking
	IEC
	IEC 60947-2
	UL 489
	UL/CSA
	CSA (Class No. 4652-06)
	CSA-C22.2 No. 5-09
	UL (Category Control Number WJAZ)
	UL (File No. E148671)
	CSA certified
	CSA (File No. 22086)
	UL listed

Product specifications

Type

Switch-disconnector

Special features

IEC/EN 60947-2: circuit breakers without overcurrent (CBI-X) with main switch characteristics and isolating characteristics to IEC/EN 60204. Rated current = rated uninterrupted current: 800 A

Application

Branch circuits, feeder circuits

Amperage Rating

800 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

N4

Features

Motor drive optional

Protection unit

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NS4](#)

Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-022.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-3d-drawing-003.eps](#)

eCAD model

[DA-CE-ETN.NS4-800-NA](#)

Installation instructions

[eaton-circuit-breaker-basic-unit-bg4-il012101zu.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CD-nzm4_3p](#)

[DA-CS-nzm4_3p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

DIN rail (top hat rail) mounting optional

Fixed

Built-in device fixed built-in technique

Equipment heat dissipation, current-dependent

71.04 W

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Rated current (Iu)

1200 A

Current rating (Iu) (UL 489 csa 22.2 no. 5.1)

1200 A

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Switch positions

I, +, 0

Degree of protection

IP20

In the area of the HMI devices: IP20 (basic protection type)

Direction of incoming supply

As required

Electrical connection type of main circuit

Screw connection

Lifespan, mechanical

10000 operations

Overvoltage category

III

Degree of protection (IP), front side

IP40 (with insulating surround)

IP66 (with door coupling rotary handle)

Degree of protection (terminations)

IP00 (terminations, phase isolator and band terminal)

IP10 (tunnel terminal)

Number of poles

Three-pole

Terminal capacity (copper strip)

Min. 6 segments of 16 mm x 0.8 mm at flat conductor terminal

Max. 10 segments of 32 mm x 1 mm (2x) at flat conductor terminal

10 segments of 50 mm x 1 mm (2x) at 1-hole module plate

Min. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched)

Max. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched)

10 segments of 80 mm x 1 mm (2x) at rear-side width extension

NA: same as for IEC

Lifespan, electrical

2000 operations at 690 V AC-1

2000 operations at 415 V AC-3

3000 operations at 400 V AC-1

1000 operations at 690 V AC-3

2000 operations at 415 V AC-1

2000 operations at 400 V AC-3

Functions

Disconnectors/main switches

Position of connection for main current circuit

Front side

Rated operational current for specified heat dissipation (In)

800 A

Short-circuit total breaktime

< 25 ms (< 415 V); < 35 ms (> 415 V)

Short-circuit release non-delayed setting - max

25000 A

Short-circuit release non-delayed setting - min

25000 A

Terminal capacity (copper busbar)

M10 at rear-side screw connection

Min. 25 mm x 5 mm direct at switch rear-side connection

Max. 50 mm x 10 mm (2x) direct at switch rear-side connection

Min. 25 mm x 5 mm at rear-side 1-hole module plate

Max. 50 mm x 10 mm (2x) at rear-side 1-hole module plate

50 mm x 10 mm (2x) at rear-side 2-hole module plate

Min. 60 mm x 10 mm at rear-side width extension

Max. 80 mm x 10 mm (2x) at rear-side width extension

NA: same as for IEC

Terminal capacity (copper stranded conductor/cable)

50 mm² - 240 mm² (4x) at 4-hole tunnel terminal

120 mm² - 185 mm² (1x) direct at switch rear-side connection

50 mm² - 185 mm² (4x) direct at switch rear-side connection

Min. 120 mm² - 300 mm² (1x) at rear-side 1-hole module plate

Max. 95 mm² - 300 mm² (2x) at rear-side 1-hole module plate

Min. 95 mm² - 185 mm² (2x) at rear-side 2-hole module plate

Max. 35 mm² - 185 mm² (4x) at rear-side 2-hole module plate

300 mm² (4x) at rear-side width extension

95 mm² - 240 mm² (6x) at rear-side width extension

NA: AWG 0- kcmil 500 (4x) at 4-hole tunnel terminal

NA: kcmil 250 - kcmil 350 (1x) direct at switch rear-side connection

NA: AWG 0 - kcmil 350 (4x) direct at switch rear-side connection

NA: min. kcmil 250 - kcmil 600 (1x) at rear-side 1-hole module plate

NA: max. AWG 3/0 - kcmil 600 (2x) at rear-side 1-hole module plate

NA: min. AWG 3/0 - kcmil 350 (2x) at rear-side 2-hole module plate

NA: max. AWG 2 - kcmil 350 (4x) at rear-side 2-hole module plate

NA: kcmil 600 (4x) at rear-side width extension

NA: AWG 3/0 - kcmil 500 (6x) at rear-side width extension

Terminal capacity (aluminum stranded conductor/cable)

Min. 185 mm² - 240 mm² (1x) at rear-side 1-hole module plate

Max. 70 mm² - 185 mm² (2x) at rear-side 1-hole module plate

50 mm² (4x) at rear-side 2-hole module plate

240 mm² (2x) at rear-side width extension

70 mm² - 240 mm² (6x) at rear-side width extension

NA: aluminum conductor not applicable

Handle type

Rocker lever

Short delay current setting (I_{sd}) - max

0 A

Short delay current setting (I_{sd}) - min

0 A

Instantaneous current setting (I_i) - max

25000 A

Instantaneous current setting (I_i) - min

25000 A

Number of operations per hour - max

60

Overload current setting (Ir) - max

0 A

Overload current setting (Ir) - min

0 A

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 230 V, 50/60 Hz

43 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 400/415 V, 50/60 Hz

35 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 440 V, 50/60 Hz

33 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 525 V, 50/60 Hz

20 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 690 V, 50/60 Hz

18 kA

Rated short-circuit making capacity Icm at 400/415 V, 50/60 Hz

154 kA

Rated short-circuit making capacity Icm at 440 V, 50/60 Hz

143 kA

Rated short-circuit making capacity Icm at 525 V, 50/60 Hz

84 kA

Rated short-circuit making capacity Icm at 690 V, 50/60 Hz

74 kA

Standard terminals

Screw connection,Optional:Tunnel terminal,Rear-side connection,Strip connection

Optional terminals

Connection on rear. Strip terminal. Tunnel terminal

Rated operating voltage Ue (UL) - max

600 V

Rated short-circuit making capacity Icm at 240 V, 50/60 Hz

187 kA

Rated impulse withstand voltage (Uimp) at auxiliary contacts

6000 V

Rated impulse withstand voltage (Uimp) at main contacts

8000 V

Rated insulation voltage (Ui)

1000 V AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia