

MAG-MATE

TE Internal #: 281623-2

Poke-In, 22 – 18 AWG Lead Wire, .326 – .8 mm² Lead Wire, Crimp / Insulation Displacement (IDC), MAG-MATE, Magnet Wire Terminals

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Poke-In**
Compatible Insulation Diameter (Max): **3 mm [.118 in]**
Compatible Insulation Diameter Range: **3 mm [.118 in]**
Lead Wire Size: **22 – 18 AWG**

Features

Product Type Features

Compatible With Discrete Wire Type	Solid, Stranded
------------------------------------	-----------------

Contact Features

Magnet Wire Terminal Type	Poke-In
Terminal Plating Material	Tin
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Crimp, Insulation Displacement (IDC)
Crimp Area Length	7.87 mm[.31 in]

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Terminal Height	3.37 mm[.133 in]
Compatible Insulation Diameter (Max)	3 mm[.118 in]
Compatible Insulation Diameter Range	3 mm[.118 in]
Lead Wire Size	22 – 18 AWG



Stock Thickness (Magnet Wire Side)	.45 mm[.018 in]
Product Length	18.4 mm[.722 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel, Reel/Carton
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1217470-1
TAB MAG-MATE POKE-IN 22-18

TE Part # 62895-1
MAG-MATE POKE-IN TAB 018 TPBR

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

Also in the Series | **MAG-MATE**

Insertion & Extraction Tools(6)

Magnet Wire Terminals(329)

PCB Terminals(1)

Customers Also Bought

TE Part #2-31518-1
TERMINAL,DG R 26-22 2

TE Part #6-62131-3
CLSTR PIN RCPT

TE Part #2232905-1
EP 2.5 LIF RCPT CONTACT, 26-22 AWG

TE Part #1-825433-0
MOD 2 PINHDR 1X10P.

TE Part #1-1393243-4
RTE24110

TE Part #794954-6
6P RCPT VAL-U-LOK V2

TE Part #794958-1
VAL-U-LOK SKT BR SN 22-26AWG

TE Part #640311-5
MINI AMP-IN 22-18 AWG POST TIN PLTD

TE Part #1217406-1
TAB RIGHT ANGLE POKEIN MAGMATE

TE Part #925819-3
MINI AMP-IN 26-22 AWG



Documents

Product Drawings
MAG-MATE TERMINALS

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_281623-2_D.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_281623-2_D.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_281623-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
Magnet Wire Terminals & Splices

English

Product Specifications
Application Specification

English