

WMS-OT HF 4,8 (EX9)R - Marking sleeve



1044243

<https://www.phoenixcontact.com/gb/products/1044243>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marking sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK W, cable diameter range: 1.6 ... 4.8 mm, unperforated, mounting type: slide-on, Number of individual labels: 1, text field height: 9 mm, text field width: 30000 mm

Your advantages

- Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- Non-shrinkable halogen-free marking sleeve on rolls, in an oval design, for marking conductors and cables
- The oval design and the large opening enable rapid fitting onto the conductor or cable
- Through the use of the cutting or perforation unit, the marking sleeve can be cut to or perforated at the desired length (max. 1 m)
- Widely used and proven worldwide in the railway industry

Commercial data

Item number	1044243
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BGE22F
Product key	BGE22F
Catalog page	Page 228 (C-3-2019)
GTIN	4055626622408
Weight per piece (including packing)	515 g
Weight per piece (excluding packing)	518 g
Customs tariff number	39173200
Country of origin	CN

WMS-OT HF 4,8 (EX9)R - Marking sleeve



1044243

<https://www.phoenixcontact.com/gb/products/1044243>

Technical data

Notes

Material information	For the THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK ROLLMASTER 300/600, and THERMOMARK E.300 (D)/E.600 (D) roll printers, this material can only be processed with an external media hub.
----------------------	--

Product properties

Product type	Conductor marking
Area of application	Railway industry

Marking

Number of individual labels	1
Identification technology	Thermal transfer for rolls

Dimensions

Width	9 mm
Length	30 m

External dimensions

Outside diameter	1.6 mm ... 4.8 mm
------------------	-------------------

Text field

Text field width	30000 mm
Text field height	9 mm

Material specifications

Color	white (RAL 9010)
Material	Polyolefine
Flammability rating according to UL 94	V0
Base element material	polyolefine
Components	halogen-free

Cable/line

External cable diameter	1.6 mm ... 4.8 mm
-------------------------	-------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

WMS-OT HF 4,8 (EX9)R - Marking sleeve



1044243

<https://www.phoenixcontact.com/gb/products/1044243>

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Specification	IEC 60068-2-2:2007-07
Result	Test passed
Duration	96 h
Temperature for testing	120 °C

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-30 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	5 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

WMS-OT HF 4,8 (EX9)R - Marking sleeve



1044243

<https://www.phoenixcontact.com/gb/products/1044243>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WMS-OT HF 4,8 (EX9)R - Marking sleeve



1044243

<https://www.phoenixcontact.com/gb/products/1044243>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk