

**BOSCH**

Invented for life

# Product data sheet

## Power tools for trade & industry

Detector

## GMS 120-27



Clear and simple: the intuitive wall scanner that makes the invisible visible

### The most important data

Max. detection depth	120 mm
Bosch Radar Technology	no
Detectable objects	magnetic metals (e.g. iron), ...

**Part Number** 0 601 081 700

## Technical data

### Technical data

Bosch Radar Technology	no
Detectable objects	magnetic metals (e.g. iron), non-magnetic metals (e.g. copper), live cables, wooden substructures
Max. detection depth	120 mm
Detection depth, magnetic metal, max.	100 mm
Detection depth, non-magnetic metal, max.	120 mm
Detection depth, live cables, max.	50 mm
Detection depth, wooden substructures, max.	30 mm
Dust and splash protection	IP 54
Material identification	Magnetic metal, Non-magnetic metal, Live cable, Non-metal material
Power supply	2 x 1.5 V LR6 (AA), 2 x 1.2 V HR6 (AA), 1 x BA 3.7V 1.0Ah Li-Ion battery
Weight, approx.	0.29 kg
Additional function	Marking hole



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Gives you confidence by detecting metal, live wires, and wooden studs behind the wall
- Easy to use with simple mode selection and marking hole
- Built for operation on tough job sites thanks to shock-absorbing rubber casing and IP54

PROTECTED TOOLS  
Impact | Water | Dust

