



Connectors > Circular Connectors > Standard Circular Connectors > M12 STRAIGHT CRIMPED STRAIN RELIEF



Connector System: **Cable-to-Cable**

Number of Positions: **4**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **4 A**

[All M12 STRAIGHT CRIMPED STRAIN RELIEF \(53\)](#)

Features

Product Type Features

|                                   |                  |
|-----------------------------------|------------------|
| Product Type                      | Connector Kit    |
| Connector System                  | Cable-to-Cable   |
| Sealable                          | Yes              |
| Connector & Contact Terminates To | Wire & Cable     |
| Circular Connector Type           | Plug             |
| Shell Type                        | Full Metal Shell |

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 4  |
| Contacts Preloaded  | No |

Electrical Characteristics

|                   |        |
|-------------------|--------|
| Operating Voltage | 50 VDC |
|-------------------|--------|

Body Features

|                          |     |
|--------------------------|-----|
| Environmental Protection | Yes |
|--------------------------|-----|



|                                             |                               |
|---------------------------------------------|-------------------------------|
| Weight                                      | 25 g[.0552 lb]                |
| Environmental Protection Type               | Elastomer Sealed              |
| Shell Plating Material                      | Nickel                        |
| Shell Base Material                         | Brass                         |
| Circular Connector Insulation Material Type | Low Fire Hazard Thermoplastic |
| Hermetically Sealed                         | Yes                           |

Contact Features

|                                 |     |
|---------------------------------|-----|
| Contact Current Rating (Max)    | 4 A |
| Circular Connector Contact Type | Pin |

Mechanical Attachment

|                         |                            |
|-------------------------|----------------------------|
| Connector Mounting Type | Cable Mount (Free-Hanging) |
| Polarization Code       | D                          |
| Mating Alignment Type   | Keyed                      |
| Mating Retention        | With                       |

Dimensions

|                                        |        |
|----------------------------------------|--------|
| Accepts Wire Insulation Diameter Range | 6.6 mm |
| Wire Size                              | 22 AWG |

Usage Conditions

|                             |                                                      |
|-----------------------------|------------------------------------------------------|
| IP Dust Sealing Level       | 6                                                    |
| IP Water Sealing Level      | 7                                                    |
| Operating Temperature Range | -40 – 70 °C, -40 – 85 °C[-40 – 158 °F][-40 – 185 °F] |

Operation/Application

|                     |            |
|---------------------|------------|
| Durability Rating   | 250 Cycles |
| Circuit Application | Signal     |
| Shielded            | Yes        |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                    |   |
|--------------------|---|
| Packaging Quantity | 1 |
|--------------------|---|

Other

|                   |     |
|-------------------|-----|
| Field Serviceable | Yes |
|-------------------|-----|



Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                                                                                                                                                                                                                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                           |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>SVHC > Threshold:<br>Pb (3.5% in Component Part)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                            |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                                                                                                                                                                                                                                                                                                                     |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-2823557-1  
CRIMP TOOL FOR CRIMP FLANGE /SLEEVE



TE Part # 1-2823560-1  
ASSEMBLY TOOL HANDLE FOR CRIMP FLANGE



TE Part # 1-2823561-1  
UNIVERSAL INSERT (ALL M12 CODES)



TE Part # CAT-M1-M1  
M12 ASSEMBLY TOOLING





TE Part # CAT-R131-IN722

CRIMP INSERT FOR USE WITH 1-2823557-1

TE Part # 601966-1

CRIMPING TOOL M22520/2-01

TE Part # 601967-1

CRIMPING TOOL M22520/1-01

Customers Also Bought

TE Part #720677-000

202K121-100-0

TE Part #165565-2

2,8 PIDG FASTON REC

TE Part #1604042-6

KIT,175A,1/0 AWG,BLACK

TE Part #326882

TERMINAL,PIDG R 16-14 6

TE Part #66740-2

TYPE XII FEMALE CONT (L.P.)

TE Part #650074-000

D-436-36

TE Part #YAFD50-16-8SNC0120

RECP ASSY

TE Part #3-1105050-1

HN.D-C-STI.AG.0,75

Documents

Product Drawings

M12 D-M-4, CRIMP, CAT5 RADOX 6.6MM, H&S

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-2823445-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2823445-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2823445-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

M12 RAIL CONNECTOR SERIES

English

M12 Rail Straight Connector

English

Product Specifications

Product Specification

English