

PRODUCT DATA SHEET

Product Ref: **TG5595**

Premium Leather Cut Resistance Driver Style Winter Glove

Key Features:

- Crafted from premium quality goat leather, this glove offers exceptional durability, and a soft touch. The leather provides a sturdy exterior that stands up to tough working conditions while offering a comfortable fit.
- Featuring a soft thermal liner, the TG5595 provides excellent insulation performance, keeping your hands warm and comfortable in cold weather. Densely knitted aramid fabric reinforcement in the palm and fingers provides superior cut & heat resistance protection.
- Comfort pads are strategically placed in areas most exposed to tough tasks, such as the palms, to maximise protection and reduce fatigue.
- The gloves are ergonomically designed to provide maximum comfort and support. The pre-curved fingers and flexible fit ensure natural hand movement and reduce strain, making them ideal for extended wear.
- The outer surface of leather is treated to be a fluorocarbon free, water-resistant finish, protecting your hands from moisture and ensuring they stay dry in wet conditions. These gloves are perfect for use in cold and wet winter conditions.
- Reinforced welted double stitching and robust materials enhance the durability of the gloves, making them resistant to wear and tear.



KEY



Dry



Wet



Heat



Oily



Cold



Chemical

Ideal for:

- Forestry & Landscaping
- Construction
- Mining & Drilling
- Utilities
- Heavy Logistics
- Plant Hire
- Demolition

Technical Specifications

Size Range: 6-12

Lining: Polyester Fleece & Aramid Fabric

Outer: Premium Grade Goat Leather

Conditions

Packaging

Qty/bag: 10 pairs

Qty/carton: 60 pairs

Certification

EN 388:2016



3 5 4 3 C

ANSI/ISEA 105:2016



CUT

EN 407:2020



4 1 2 1 X X

EN 511:2006



1 1 X



T +44 (0)1344 207090

T (313) 518-5588

[traffiglove.com](http://www.traffiglove.com)

Traffi
FOR HANDS. FOR LIFE.