


## Flame Retardant Cable

# GX32CAB/100



It is vital that the highest quality cable is used to ensure the integrity and longevity of any system.

High quality cable with installer friendly characteristics, pliable, easy to strip and make off connections.

Flame retardant cable fully compliant to IEC 60332-3-24 regulations designed to resist the spread of fire vertically within a building.

This 2 core flame retardant cable can be specified on installations that have a risk of fire spreading between floors.

## Specifications

Core	1 x 0.76
Resistance	38 Ohms/Km
Conductor Area	0.454mm <sup>2</sup>
Material	Solid Copper
Core Insulation	PVC Type R2
Sheathing	PVC Type RZ
Operating Temp	-20 to +85° C
Screening	Aluminium / pet foil
Drain Wire	Soft tinned copper
Jacket is flame retardant to CEI 20-22	