



**6002**

SKF Explorer

**Dimensions**

d	15	mm
D	32	mm
B	9	mm
$d_1$	≈ 20.5	mm
$D_2$	≈ 28.2	mm
$r_{1,2}$	min. 0.3	mm

**Abutment dimensions**

$d_a$	min.	17	mm
$D_a$	max.	30	mm
$r_a$	max.	0.3	mm

**Calculation data**

Basic dynamic load rating C	5.8	kN
Basic static load rating $C_0$	2.8	kN
Fatigue load limit $P_u$	0.12	kN
Reference speed	50000	r/min
Limiting speed	32000	r/min
Calculation factor $k_r$	0.025	
Calculation factor $f_0$	14	

**Mass**

Mass bearing	0.0296	kg
--------------	--------	----