



HS-26 SOLDERING IRON

Rated voltage / frequency	100 V (HS-26) 230 V (HS-26-230)
Power consumption	50 W
Setting temperature	200 to 500°C
Standard tip	HS-132
OAL	200 mm (not including the cord)
Weight	75 g (not including the cord)



HS-26 Temperature characteristics



Replacement parts

HS-130 HEATER

100 V 230 V

HS-130-230




SOLDERING TIPS (for HS-26)



* Custom-order tip shapes and sizes are possible.


HS-131

■ B type




HS-132

■ B type




HS-133

■ B type




HS-134

■ B type




HS-135

■ C type




HS-136

■ C type




HS-137

■ C type



HS-138

■ C type



HS-139

■ C type




HS-140

■ C type




HS-141

■ D type




HS-142

■ D type




HS-143

■ D type



HS-144

■ D type



HS-145

■ D type

