




Aurora Bearing Company
901 Aucutt Rd.
Montgomery, IL 60538
Phone: 630.859.2030 • **Fax:** 630.859.0971
Email: customersupport@aurorabearing.com • **Website:** www.aurorabearing.com

Item # XB-8, XM & XB Series Male Rod Ends, Extra Strength - Heavy Duty Shank (PTFE Liners Available)

- Body - Low carbon steel protective coated for corrosion resistance.
- Ball - Alloy steel, heat treated, hard chrome plated.
- Race - Alloy steel, heat treated protective coated for corrosion resistance. (Low carbon steel with PTFE liners).
- All sizes solid shank type.
- Grease Fitting available for all sizes. Units are supplied without grease fittings. When a grease fitting is required, specify by adding suffix "Z" or "F". Ex.: XM-6Z = Zerk Type Fitting XM-6F = Flush Type Fitting.
- Load ratings apply

+ [more](#)

[Specifications](#) | [XM & XB Note](#)

Specifications	
Thread Type	Left Hand
Thread Configuration	Male
B - Ball Bore	.5000 in
W - Ball Width	.625 in
H - Head Width	.500 in
A - Base to Center	2.625 in
D - Head Diameter	1.500 in
Ball Diameter	.937 in
C - Thread Length	1.625 in
Thread Size	5/8-18

Thread Class	UNF-3A-LH
a - Misalignment Angle Clevis Mounted	10 °
Ultimate Radial Static Load Capacity	12,807 lbs
Approximate Brg. Weight	0.38 lb
Options	Stud
Type of Lubrication	None

XM & XB Note

For dimensional tolerances of listed features, see the PDF version of the catalog under the "View Product Catalogs" tab from the home page.