



2.5-4

E0845010

Cable Lug KR, 2.5mm², M4



Product Properties:

Suitable for Class 2 conductor	Yes
Suitable for Class 5 conductor	Yes
Suitable for Class 6 conductor	Yes
Insulated	No
Max. current (I _{max})	30 A
Number of mounting holes	1 .
Flange shape	Ring shape
Colour insulation	Other
Slender flange model	No
With sight-hole	Yes
Conductor category	Several
Max Temp	150 °C
Surface protection	Tinned
Material	Copper
Connecting angle	180° (horizontal)
Series	KR/KS (0.75-6mm ²)

Dimensions:

HS	4.3 mm
ID	2.3 mm
OD	4.2 mm
T	1.3 mm

P1	3.5 mm
P2	5 mm
L	18 mm
N	5.5 mm
W	7.5 mm
MOQ	100 .
Unit	pcs
Bolt dimension (metric)	4 .
Nominal cross section	2.5 mm ²
Series	KR/KS (0.75-6mm2)

Approvals:

Approved according to CE	Yes
Approved according to DNV	Yes

Compliance:

CA Proposition 65	In compliance
Conflict Minerals	Contain "Tin"
Extended Minerals	Contain "Copper"
Iron and Steel Sanction	In compliance
PFAS	No PFAS
POPs	No POPs
REACH	No SVHC (Latest. 05 Nov 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC001051 - Tube cable lug for copper conductors
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Cable lugs
Search Description	RÖRKABELSKO KR
Alternative SKU	2.5-4
E-no	E0845010

Logistic information:

Barcode	733117612004
Country of origin	IN
E-no	E0845010

Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	100 .
Stock code	2.5-4
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.