



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 27519627788) Decamethylcyclopentasiloxane (D5) (.5% in 27519627788) Octamethylcyclotetrasiloxane (D4) (.5% in 27519627788) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1924537-1  
TPA, CAP, 6 POSITION, 2X3 SEALED, 0.64mm

TE Part # 1924536-1  
CAP HOUSING, 6 POS, 2X3, SEALED, 0.64mm

TE Part # 1924538-1  
SEAL COVER, CAP, 6 POS, 2X3, SEALED, .64

TE Part # 1924211-1  
ASSY, PLUG, 2X3, SEALED, 0.64, OPEN

TE Part # CAT-N57-GYTH68  
Generation Y Terminals, 68POS Hybrid

TE Part # 2-1924211-1  
ASSY, PLUG, 2X3, SEALED, 0.64, OPEN,CPA

TE Part # 1924211-3  
ASSY, PLUG, 2X3, SEALED, 0.64, BLKD

Customers Also Bought

TE Part #350417-1  
.093 COMM P&S SOK 18-24 PTPBR

TE Part #179631-2  
DIAGNOSTIC PLUG HSG 16P BLACK

TE Part #CAT-M4595-T273  
MCON Receptacle and Tab

TE Part #770252-1  
UMNL II PIN PTPBR LP 24-18

TE Part #770009-1  
UMNL II PIN PTPBR

TE Part #90548-1  
ASSY PRO-CRIMPER UNIV M-N-L

TE Part #770027-1  
06P UMNLI IN-LINE CAP HSG KIT

TE Part #1586860-1  
06P UMNL CAP HSG, GW

TE Part #2301462-1  
30POS,HYBRID,REC HSG ASSY,SLD, COD A

Documents



Product Drawings

ASSY, CAP, 2X3, SEALED, 0.64, OPEN

English

CAD Files

Customer View Model

ENG\_CVM\_1924212-1\_B1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_1924212-1\_B1.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_1924212-1\_B1.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English