

Cable marker - MM-WMTB HF (55X25)R C1 YE/BK - 1116210

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 55 mm x 22 mm, Number of individual labels: 20

Product Description


Prepunched, halogen-free MM-WMTB HF conductor markers made of polyurethane are attached to the conductor with a cable tie.

Your advantages

- The pre-punched geometry enables easy and convenient use
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The cable markers are mounted very easily using a cable tie. Alternatively, a large number of conductors can also be bundled together in this way
-



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 042226
GTIN	4063151042226
Weight per Piece (excluding packing)	83.400 g
Custom tariff number	96121010
Country of origin	China
Sales Key	BG221E

Technical data

Dimensions

Length (b)	26 mm
Width (a)	75 mm
Cable diameter	≥ 6 mm

Cable marker - MM-WMTB HF (55X25)R C1 YE/BK - 1116210

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
---------------------------------	------------------

General

Color	yellow/black
Components	free from silicone, halogen, and cadmium
Material	Polyurethane
Flammability rating according to UL 94	HB
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	20
Marking mounting type	Assembly with cable binders
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 9.0	27400401

ETIM

ETIM 7.0	EC001530
----------	----------

Accessories

Accessories

Cable marker - MM-WMTB HF (55X25)R C1 YE/BK - 1116210

Accessories

Cable tie

Cable tie - WT-HF 4,5X200 - 3240760



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X200 BK - 3240761



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X160 - 3240756



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X160 BK - 3240757



Cable binders for quick and secure bundling, standard version

Cable tie - WT-ID HF 4,5X200 BU - 3240797



Cable binders for quick and secure fastening, can be detected using metallic pigments
