

# Set of cable gland + nut stainless steel M16 AISI304L, IP68, UL approved

NSYCGX16

EAN Code: 3606481360229

### Main

Range	PanelSeT	
Product or component type	Cable gland	
Accessory / separate part category	Cable management accessory	
Range compatibility	PanelSeT PanelSeT CRN PanelSeT PanelSeT S3D PanelSeT PanelSeT S3X	
Mounting location	Enclosure bottom Enclosure top	
Cable entry	Cable gland M16	
Device composition	1 cable gland 1 lock nut 1 seal	
Quantity per set	Set of 5	
Material	Seal: CR (chloroprene) Body: stainless steel AISI 304L	

## Complementary

Colour	Grey
Fixing mode	Screwed By nut
Height	30 mm
Net weight	0.019 kg

## **Environment**

Product certifications	VDE	
Flame retardance	V2 conforming to UL 94	
Ambient air temperature for operation	-20100 °C permanent -40150 °C intermittent	
IP degree of protection	IP68 conforming to IEC 60529 5 bar, 30 min	

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	2.000 cm
Package 1 Length	3.000 cm

Package 1 Weight	23.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Height	11.000 cm
Package 2 Width	28.500 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.682 kg
Unit Type of Package 3	P12
Number of Units in Package 3	2400
Package 3 Height	40.700 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	79.500 ka

# **Logistical informations**

Country of origin

# **Contractual warranty**

Warranty 18 months

27 Mar 2025



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	

### **Use Again**

○ Repack and remanufacture		
Take-back	No	