


FEATURES

- **Fluorinated Ethylene Propylene material:** Provides excellent chemical resistance and durability
- **Shore A hardness of 90 to 95:** Ensures robust performance in various applications
- **Wide temperature range (-20 °C to 140 °C):** Suitable for diverse environmental conditions
- **Compliant with multiple standards:** Meets BS ISO 3601-1, AS 568, and other key standards for quality assurance
- **Viton and Fluoroelastomer options:** Offers flexibility in material choice for specific needs

RS PRO 139.07 mm O-Ring Seal, Fluorinated Ethylene Propylene

RS Stock No: 731-411



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for high-performance sealing applications, offering excellent chemical resistance and durability. Ideal for use in demanding environments, it ensures reliable sealing under a wide range of temperatures.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	139.07 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	149.73 mm
Thickness	5.33 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

