

# TECHNICAL DATA SHEET

Update of the document : 08/06/2015  
ISO reference of the document: DON/LS 03.4129.A



LEMAITRE SECURITE SAS  
17 rue Bitschhoffen  
CS 90024  
F 67350 La Walck FRANCE  
Tél. : +33 (0)3 88 72 28 80  
Fax : +33 (0)3 88 07 05 37  
[www.lemaitre-securite.com](http://www.lemaitre-securite.com)  
[info@lemaitre-securite.com](mailto:info@lemaitre-securite.com)



## RESEDA GREY S1P SRC

LOW SHOE IN LIGHTWEIGHT AND BREATHABLE  
HONEYCOMB TEXTILE

### PROTECTIONS FOR THIS MODEL



Available sizes : from 37 (4) to 42 (8)  
Poids par paire taille 37 : 650 gr.

Norm EN ISO 20345 : 2011  
AET N° 0075/007/161/06/15/0623  
EXT 02/06/15

### Upper features

- Upper : lightweight and breathable honeycomb textile
- Tongue : lightweight and breathable honeycomb textile
- Quarter lining : black three-dimensional micro-porous textile
- Vamp lining : synthetic
- Backpart : synderm
- Closing : plastic eyelets
- Laces : polyamid
- Tongue markings : size, manufacturer, manufacture date (month, year), norm, protection, CE marking.

### Protections 100% COMPOSITE

- Toecap : polycarbonate
- Anti-perforation insert : high tenacity composite fabric « 0 » penetration

### Fitting features

- Natur'form (large)
- Lasting : California
- Lasting insole : textile
- Footbed : foam and textile

### Sole features

- Name : PARABOLIGHT
- Material : dual density polyurethane
- Comfort sole density : 0,5
- Comfort sole color : dark grey
- Outsole density : 1
- Outsole color : black
- Slip resistance SRA (flat) : 0,33 ; (heel) : 0,36
- Slip resistance SRB (flat) : 0,23 ; (talon) : 0,21



### Basics and additional requirements of the norm EN ISO 20345 : 2011

	Steel toecap		Polycarbonate toecap		Aluminium toecap (200 joules)
	Stainless steel		composite (high tenacity fabric)		
	A	Antistatic footwear.			
	CI	Cold insulation of sole complex.			
	E	Energy absorption of seat region.			
	FO	Resistance of the outsole to fuel oil.			
	HI	Heat insulation of sole complex.			
	HRO	Resistance of the outsole to hot contact.			
	M	Metatarsal protection.			
	P	Penetration resistance			
	WRU	Water penetration and water absorption resistant upper.			
	WR	Water resistant footwear.			



Regarding the norm EN ISO 20345, the minimum results for slip resistance to get the SRC certificate are :  
SRA (flat) ≥ 0,32  
SRA (heel) ≥ 0,28  
SRB (flat) ≥ 0,18  
SRB (heel) ≥ 0,13

### Advantages = End users benefits

Trendy safety shoe for women  
with 100% composite protections.

- **Well fitting adapted to the morphology of the female foot.**
- **Honeycomb textile** : lightweight and breathable thanks to its honeycomb structure.
- **Three-dimensional micro-porous textile as lining** : High breathability thanks to its structure that allows better ventilation of sweat. It is flexible and it improves comfort.
- **Anti-perforation insert high tenacity composite fabric « 0 » penetration** : ultra-light, ultra-flexible (insensitive to worn), thermally insulating (insensitive to temperature transfers) and protects 100% of the surface of the foot.
- **Polyurethane with good properties** : good antistatic properties and good resistance to hydrolysis and heat.
- **PARABOLIGHT sole** :
  - ✓ **Slip resistant** sole thanks to a structured drawing "winter tire" design, which allows a quick evacuation of liquids.
  - ✓ **Special design to suit the shape of women's feet for a better fit.**
  - ✓ Polyurethane Double Density (PU2D) injected : **the best dual density polyurethanes** for the insole and outsole.
- **PARABOLIC® sole** :
  - ✓ **Exceptional grip** : the concave structure of the sole allows progressive bending of the sole in order to optimize grip.
  - ✓ **Comfort when walking** : the spring effect gives a more dynamic walk and facilitates walking.
  - ✓ **Anti-fatigue** : with every step, the recycled energy gives you a spring in your step and provides anti-fatigue effect to your legs.