



Heat Shrink Tubing > NETM1000 Heat Shrink Tubing



Tubing Product Type: **Heat Shrink Tubing**

Primary Product Color: **Black**

Wall Type: **Single Wall**

Primary Product Material: **Crosslinked Polyolefin**

Expanded Inside Diameter (Min): **5 mm [.197 in]**

[All NETM1000 Heat Shrink Tubing \(10\)](#)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Body Features

Fluid Type	(ATF) Automatic Transmission Fluid, Antifreeze, Brake Fluid, Diesel Fuel, Motor Oil, Power Steering Fluid, Unleaded Gasoline
Primary Product Color	Black
Primary Product Material	Crosslinked Polyolefin

Dimensions

Expanded Inside Diameter (Min)	5 mm[.197 in]
--------------------------------	---------------

Usage Conditions

Tubing Flammability Type	Flame-Retardant
Operating Temperature Range	-55 – 135 °C

Operation/Application

Mechanical Resistance	Fluids, Strain Relief, Wrinkling
-----------------------	----------------------------------

Packaging Features

--	--



Packaging Method	Spool
------------------	-------

Other

Product Source	US
----------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | RAYCHEM NETM1000



Heat Shrink Tubing(10)



Single Wall Tubing(10)


Customers Also Bought



TE Part #1394132-1
BLINDSTOPFEN F.D3,6



TE Part #6-160448-2
FF 250 REC 1.0-2.5MM2 TPPB



TE Part #967634-1
2. RETAINER FOR 18POS



TE Part #1-1393315-1
V23132B2002B200=HCR



TE Part #DTM06-12SA-E007
PLG, 12P, GRY, N, XCAP, A



TE Part #2381114-1
SDE F AMP MCP 6.3/4.8K 4.0-6.0mm2 ASSY

Documents

Product Drawings

NETM1000-5-0-SP

English

Datasheets & Catalog Pages

Measuring_Single_Wall_Tubing

English

Selecting_Correct_Tubing_1216

English

NETM Pages from 1654296-3

English

Product Specifications

Application Specification

English