



power contactor AC-1 690 A / 690 V / 40 °C 3-pole, U_c: 72 V DC (0.7-1.25) PLC
input 24-110 V DC drive: electronic auxiliary contacts 2 NO + 2 NC main circuit:
busbar control and auxiliary circuit: spring-loaded terminal extended rated condition
railroad IEC 60077

| | |
|--|--|
| product brand name | SIRIUS |
| product designation | Power contactor |
| design of the product | With extended operating range |
| product type designation | 3RT14 |
| General technical data | |
| size of contactor | S12 |
| product extension | |
| • function module for communication | No |
| • auxiliary switch | Yes |
| power loss [W] for rated value of the current | |
| • at AC in hot operating state | 165 W |
| • at AC in hot operating state per pole | 55 W |
| • without load current share typical | 3.6 W |
| type of calculation of power loss depending on pole | quadratic |
| insulation voltage | |
| • of main circuit with degree of pollution 3 rated value | 1 000 V |
| • of auxiliary circuit with degree of pollution 3 rated value | 500 V |
| surge voltage resistance | |
| • of main circuit rated value | 8 kV |
| • of auxiliary circuit rated value | 6 kV |
| maximum permissible voltage for protective separation between coil and main contacts according to EN 60947-1 | 690 V |
| shock resistance for railway applications according to EN 61373 | Category 1, Class B |
| shock resistance at rectangular impulse | |
| • at DC | 8,5g / 5 ms, 4,2g / 10 ms |
| shock resistance with sine pulse | |
| • at DC | 13,4g / 5 ms, 6,5g / 10 ms |
| mechanical service life (operating cycles) | |
| • of contactor typical | 10 000 000 |
| • of the contactor with added electronically optimized auxiliary switch block typical | 5 000 000 |
| • of the contactor with added auxiliary switch block typical | 10 000 000 |
| reference code according to IEC 81346-2 | Q |
| Substance Prohibitance (Date) | 09/06/2016 |
| SVHC substance name | Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol - 79-94-7 Perfluorobutane sulfonic acid (PFBS) and its salts - - |
| Net Weight | 10.199 kg |
| Ambient conditions | |

| | |
|---|---------------------|
| installation altitude at height above sea level maximum | 2 000 m |
| ambient temperature | |
| • during operation | -40 ... +70 °C |
| • during storage | -55 ... +80 °C |
| relative humidity minimum | 10 % |
| relative humidity at 55 °C according to IEC 60068-2-30 maximum | 95 % |
| Main circuit | |
| number of poles for main current circuit | 3 |
| number of NO contacts for main contacts | 3 |
| number of NC contacts for main contacts | 0 |
| operating voltage | |
| • at AC-3 rated value maximum | 690 V |
| operational current | |
| • at AC-1 at 400 V at ambient temperature 40 °C rated value | 690 A |
| • at AC-1 | |
| — up to 690 V at ambient temperature 40 °C rated value | 690 A |
| — up to 690 V at ambient temperature 60 °C rated value | 600 A |
| • at AC-2 at 400 V rated value | 170 A |
| • at AC-3 | |
| — at 400 V rated value | 170 A |
| — at 500 V rated value | 170 A |
| — at 690 V rated value | 170 A |
| minimum cross-section in main circuit | |
| • at maximum AC-1 rated value | 480 mm ² |
| • at maximum Ith rated value | 480 mm ² |
| operational current | |
| • at 1 current path at DC-1 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 33 A |
| — at 220 V rated value | 3.8 A |
| — at 440 V rated value | 0.9 A |
| — at 600 V rated value | 0.6 A |
| • with 2 current paths in series at DC-1 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 500 A |
| — at 220 V rated value | 500 A |
| — at 440 V rated value | 4 A |
| — at 600 V rated value | 2 A |
| • with 3 current paths in series at DC-1 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 500 A |
| — at 220 V rated value | 500 A |
| — at 440 V rated value | 11 A |
| — at 600 V rated value | 5.2 A |
| • at 1 current path at DC-3 at DC-5 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 3 A |
| — at 220 V rated value | 0.6 A |
| — at 440 V rated value | 0.18 A |
| — at 600 V rated value | 0.125 A |
| • with 2 current paths in series at DC-3 at DC-5 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 500 A |
| — at 220 V rated value | 2.5 A |
| — at 440 V rated value | 0.65 A |
| — at 600 V rated value | 0.37 A |

| | |
|---|--|
| <ul style="list-style-type: none"> • with 3 current paths in series at DC-3 at DC-5 <ul style="list-style-type: none"> — at 24 V rated value — at 110 V rated value — at 220 V rated value — at 440 V rated value — at 600 V rated value | <p>500 A</p> <p>500 A</p> <p>500 A</p> <p>1.4 A</p> <p>0.75 A</p> |
| operating power <ul style="list-style-type: none"> • at AC-2 at 400 V rated value • at AC-3 <ul style="list-style-type: none"> — at 230 V rated value — at 400 V rated value — at 500 V rated value — at 690 V rated value | <p>90 kW</p> <p>160 kW</p> <p>90 kW</p> <p>110 kW</p> <p>160 kW</p> |
| short-time withstand current in cold operating state up to 40 °C <ul style="list-style-type: none"> • limited to 1 s switching at zero current maximum • limited to 5 s switching at zero current maximum • limited to 10 s switching at zero current maximum • limited to 30 s switching at zero current maximum • limited to 60 s switching at zero current maximum | <p>7 484 A; Use minimum cross-section acc. to AC-1 rated value</p> <p>7 484 A; Use minimum cross-section acc. to AC-1 rated value</p> <p>5 978 A; Use minimum cross-section acc. to AC-1 rated value</p> <p>3 765 A; Use minimum cross-section acc. to AC-1 rated value</p> <p>2 887 A; Use minimum cross-section acc. to AC-1 rated value</p> |
| no-load switching frequency <ul style="list-style-type: none"> • at DC | <p>500 1/h</p> |
| operating frequency <ul style="list-style-type: none"> • at AC-1 maximum | <p>600 1/h</p> |
| operating frequency <ul style="list-style-type: none"> • at DC-1 maximum | <p>250 1/h</p> |
| Ratings for railway applications | |
| thermal current (I_{th}) up to 690 V <ul style="list-style-type: none"> • up to 40 °C according to IEC 60077 rated value • up to 70 °C according to IEC 60077 rated value | <p>690 A</p> <p>520 A</p> |
| Control circuit/ Control | |
| type of voltage | DC |
| type of voltage of the control supply voltage | DC |
| control supply voltage at DC rated value | 72 V |
| operating range factor control supply voltage rated value of magnet coil at DC <ul style="list-style-type: none"> • initial value • full-scale value | <p>0.7</p> <p>1.25</p> |
| consumed current at PLC-control input according to IEC 60947-1 maximum | 2 mA |
| voltage at PLC-control input | 24 ... 110 V |
| design of the surge suppressor | with varistor |
| closing power of magnet coil at DC | 800 W |
| holding power of magnet coil at DC | 3.6 W |
| closing delay <ul style="list-style-type: none"> • at DC | <p>60 ... 90 ms</p> |
| opening delay <ul style="list-style-type: none"> • at DC | <p>80 ... 100 ms</p> |
| arcing time | 10 ... 15 ms |
| control version of the switch operating mechanism | PLC-IN or Standard A1 - A2 (adjustable) |
| Auxiliary circuit | |
| number of NC contacts for auxiliary contacts <ul style="list-style-type: none"> • instantaneous contact | <p>2</p> <p>2</p> |
| number of NO contacts for auxiliary contacts <ul style="list-style-type: none"> • instantaneous contact | <p>2</p> <p>2</p> |
| operational current at AC-12 maximum | 10 A |
| operational current at AC-15 <ul style="list-style-type: none"> • at 230 V rated value • at 400 V rated value • at 500 V rated value | <p>6 A</p> <p>3 A</p> <p>2 A</p> |

| | |
|---|--|
| operational current at DC-12 | |
| <ul style="list-style-type: none"> ● at 24 V rated value ● at 48 V rated value ● at 60 V rated value ● at 110 V rated value ● at 125 V rated value ● at 220 V rated value ● at 600 V rated value | 10 A 6 A 6 A 3 A 2 A 1 A 0.15 A |
| operational current at DC-13 | |
| <ul style="list-style-type: none"> ● at 24 V rated value ● at 48 V rated value ● at 60 V rated value ● at 110 V rated value ● at 125 V rated value ● at 220 V rated value ● at 600 V rated value | 6 A 2 A 2 A 1 A 0.9 A 0.3 A 0.1 A |
| UL/CSA ratings | |
| full-load current (FLA) for 3-phase AC motor | |
| <ul style="list-style-type: none"> ● at 480 V rated value ● at 600 V rated value | 180 A 192 A |
| yielded mechanical performance [hp] | |
| <ul style="list-style-type: none"> ● for 3-phase AC motor <ul style="list-style-type: none"> — at 220/230 V rated value — at 460/480 V rated value — at 575/600 V rated value | 75 hp 150 hp 200 hp |
| contact rating of auxiliary contacts according to UL | A600 / Q600 |
| Short-circuit protection | |
| design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V | C characteristic: 10 A; 0.4 kA |
| design of the fuse link | |
| <ul style="list-style-type: none"> ● for short-circuit protection of the main circuit <ul style="list-style-type: none"> — with type of coordination 1 required — with type of coordination 2 required ● for short-circuit protection of the auxiliary switch required | gG: 800 A (690 V, 50 kA) gR: 710 A (690 V, 100 kA) gG: 10 A (500 V, 1 kA) |
| Installation/ mounting/ dimensions | |
| mounting position | with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back |
| fastening method side-by-side mounting | Yes |
| fastening method | screw fixing |
| height | 214 mm |
| width | 160 mm |
| depth | 225 mm |
| required spacing | |
| <ul style="list-style-type: none"> ● with side-by-side mounting <ul style="list-style-type: none"> — forwards — upwards — downwards — at the side ● for grounded parts <ul style="list-style-type: none"> — forwards — upwards — at the side — downwards ● for live parts <ul style="list-style-type: none"> — forwards — upwards — downwards — at the side | 20 mm 10 mm 10 mm 10 mm 20 mm 10 mm 10 mm 10 mm 20 mm 10 mm 10 mm 10 mm |
| Connections/ Terminals | |

| | |
|--|---|
| type of electrical connection | |
| <ul style="list-style-type: none"> • for main current circuit • for auxiliary and control circuit | <p>screw-type terminals</p> <p>spring-loaded terminals</p> |
| width of connection bar | 25 mm |
| thickness of connection bar | 6 mm |
| diameter of holes | 11 mm |
| number of holes | 1 |
| type of connectable conductor cross-sections | |
| <ul style="list-style-type: none"> • for main contacts <ul style="list-style-type: none"> — solid or stranded • for AWG cables for main contacts | <p>2x (70 ... 240 mm²)</p> <p>2/0 ... 500 kcmil</p> |
| type of connectable conductor cross-sections | |
| <ul style="list-style-type: none"> • for auxiliary contacts <ul style="list-style-type: none"> — solid — solid or stranded — finely stranded with core end processing — finely stranded without core end processing • for AWG cables for auxiliary contacts | <p>2x (0.25 ... 2.5 mm²)</p> <p>2x (0,25 ... 2,5 mm²)</p> <p>2x (0.25 ... 1.5 mm²)</p> <p>2x (0.25 ... 2.5 mm²)</p> <p>2x (24 ... 14)</p> |
| AWG number as coded connectable conductor cross section for auxiliary contacts | 24 ... 14 |

Safety related data

| | |
|---|----------------------|
| product function | |
| <ul style="list-style-type: none"> • mirror contact according to IEC 60947-4-1 • positively driven operation according to IEC 60947-5-1 | <p>Yes</p> <p>No</p> |

Electrical Safety

| | |
|--|--|
| protection class IP on the front according to IEC 60529 | IP00; IP20 with box terminal/cover |
| touch protection on the front according to IEC 60529 | finger-safe, for vertical contact from the front with box terminal/cover |

Communication/ Protocol

| | |
|---|----|
| product function bus communication | No |
|---|----|

Approvals Certificates

| | |
|--------------------|--------------------------|
| Environment | General Product Approval |
|--------------------|--------------------------|

[Environmental Conformations](#)



| | | | |
|------------|--------------------------|--------------------------|--------------|
| EMV | Functional Safety | Test Certificates | other |
|------------|--------------------------|--------------------------|--------------|



[Type Examination Certificate](#)

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



[Confirmation](#)

| | |
|--------------|----------------|
| other | Railway |
|--------------|----------------|

[Miscellaneous](#)

[Special Test Certificate](#)

Further information

- Information on the packaging**
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
- Information for data generation and storage**
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
- Information- and Downloadcenter (Catalogs, Brochures,...)**
<https://www.siemens.com/ic10>
- Industry Mall (Online ordering system)**
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT1476-2XJ46-0LA2>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3RT1476-2XJ46-0LA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT1476-2XJ46-0LA2&lang=en

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT1476-2XJ46-0LA2>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)





last modified:

12/7/2025 