

FEATURES

- **High chemical resistance:**
Suitable for a wide range of chemicals, enhancing versatility
- **Maximum operating pressure of 3000 kPa:**
Ensures suitability for high-pressure applications
- **Maximum operating temperature of 280 °C:**
Capable of withstanding extreme temperatures
- **Rotary speed of 18 m/s:**
Supports high-speed applications
- **Section size of 16 mm:**
Provides a robust sealing solution

RS PRO 8m Polytetrafluoroethylene Gland Packing

RS Stock No: 606-549



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from high-quality polytetrafluoroethylene, it provides excellent chemical resistance and durability. Ideal for use in high-pressure and high-temperature settings, it ensures reliable performance and longevity.

General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	16 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------