



Light Indicator 1x LED 12..60V red

Model			
product brand name		SETRON	
product designation		5TE5 indicator lights	
design of the product		LED signal detector	
type of light source		LED	
socket design for light source		others	
type of voltage of the operating voltage		AC/DC	
Supply voltage			
operating voltage			
• rated value minimum			
• rated value maximum			
• at AC rated value			
Protection class			
protection class IP		IP20	
Appearance			
color of the lens		red	
Number			
number of terminals with cross-head screw		1	
Connections			
connectable conductor cross-section for flexible conductor with core end processing			
• minimum			
• maximum		1 mm²	
		6 mm²	
connectable conductor cross-section for rigid conductor			
• minimum			
• maximum		1.5 mm²	
		6 mm²	
tightening torque with screw-type terminals maximum		1.2 N·m	
Mechanical Design			
height		90 mm	
depth		64 mm	
installation depth		70 mm	
number of modular width units		1	
Environmental conditions			
ambient temperature during operation			
• minimum			
• maximum			
		-5 °C	
		40 °C	
Approvals Certificates			
General Product Approval		other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Environment

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TE5810>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TE5810>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TE5810

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/12/2025

