

DEWALT®

18V XR WITH **FLEX VOLT** ADVANTAGE

RANGE BROCHURE

WITH DEWALT
THE TOUGH GET TOUGHER

TAKE
ADVANTAGE
OF **MORE POWER** **18VOLT**

www.DEWALT.co.uk

GUARANTEED TOUGH.®




TAKE ADVANTAGE OF MORE POWER 18VOLT

“

WHEN A DEMANDING JOB REQUIRES AN EXTRA BOOST IN PERFORMANCE, DEWALT XR FLEXVOLT ADVANTAGE HAS IT COVERED. THIS REVOLUTIONARY TECHNOLOGY HAS BEEN DESIGNED BY DEWALT ENGINEERS TO ENABLE 18V XR TOOLS WITH FLEXVOLT ADVANTAGE TO RECOGNIZE AN XR FLEXVOLT BATTERY, UNLOCKING UP TO 77% MORE POWER* WHEN NEEDED TO COMPLETE MORE CHALLENGING APPLICATIONS.

”



*Using DCB546 6Ah XR FLEXVOLT battery vs. DCB184 5Ah 18V XR battery.



18V XR Anglegrinder
DCG409
Power output by using
5.0 Ah battery

18V XR Anglegrinder
Flexvolt Advantage DCG409
Power output by using
6.0 Ah battery

Up to
+54%
more power

1011 W

1.553 W



18V XR Hammer drilldriver
DCD999
Power output by using
5.0 Ah battery

18V XR Hammer drilldriver
Flexvolt Advantage DCD999
Power output by using
6.0 Ah battery

Up to
+42%
more power

860 W

1.219 W



18V XR Recipsaw
DCS386
Power output by using
5.0 Ah battery

18V XR Recipsaw
Flexvolt Advantage DCS386
Power output by using
6.0 Ah battery

Up to
+50%
more power

982 W

1.475 W



18V XR Circularsaw
DCS573
Power output by using
5.0 Ah battery

18V XR Circularsaw
Flexvolt Advantage DCS573
Power output by using
6.0 Ah battery

Up to
+77%
more power

975 W

1.727 W



**UP TO 42%
MORE
POWER***

TAKE ADVANTAGE OF MORE POWER

**XR
BATTERY
DCB184
5.0 AH**



**POWER OUTPUT
860 WATT**

Power output by
using 5.0 Ah battery

18V XR WITH **FLEXVOLT** ADVANTAGE



**POWER OUTPUT
1219 WATT**

Power output by
using 6.0 Ah battery

**XR FLEX
VOLT
BATTERY
DCB546
6.0 AH**



**DCD999 - 18V XR XRP HAMMER
DRILL DRIVER WITH FLEXVOLT
ADVANTAGE**

The DCD999 delivers up to 42% more power when paired with a DCB546 XR FLEXVOLT 6.0 Ah battery versus a DCB184 18V XR 5.0 Ah battery. Engineered for speed and durability, other features include an all metal 3 speed transmission, DEWALT built brushless motor and full metal ratcheting chuck with carbide inserts.

SPECIFICATIONS

Power	18 volt
Max. Torque	112 Nm
Max. drilling capacity	Wood 55 / Metal 15 / Masonry 13 mm
No load speed drill	0 - 450 / 1300 / 2000 rpm
No load speed hammer	0 - 500 / 1500 / 2250 rpm
Beats per minute	38250 bpm
Weight	3.7 kg

ART.NR. PRODUCTDESCRIPTION

DCD999NT-XJ	18V XR FVA Hammer Drill Driver TSTAK, bare unit
DCD999T1-QW	18V XR FVA Hammer Drill Driver TSTAK 1 X 6.0 Ah
DCD999X1-QW	18V XR FVA Hammer Drill Driver TSTAK 1 X 9.0 Ah



UP TO **54%**
MORE POWER*



TAKE ADVANTAGE OF MORE POWER

XR
BATTERY
DCB184
5.0 AH



POWER OUTPUT
1011 WATT

Power output by using 5.0 Ah battery



POWER OUTPUT
1553 WATT

Power output by using 6.0 Ah battery

XR FLEXVOLT
BATTERY
DCB546
6.0 AH



DCG409 - 18V XR 125MM ANGLE GRINDER WITH FLEXVOLT ADVANTAGE

The DCG409 delivers up to 54% more power when paired with a DCB546 XR FLEXVOLT 6.0 Ah battery versus a DCB184 18V XR 5.0 Ah battery. Part of the DEWALT Perform & Protect range, the DCG409 incorporates an integrated Kickback Brake and the Anti-Rotation E-CLUTCH System for enhanced user protection.

SPECIFICATIONS

Power	18 volt
Max. Disc diameter	125 mm
Spindle thread	M14
No load speed	9000 rpm
Hand arm vibration	Grinding 8.3 m/s ²
Weight	2,8 kg

ART.NR.

PRODUKTBEKRIVELSE

DCG409NT-XJ	18V XR FVA anglegrinder 125 mm TSTAK, bare unit
DCG409T1-QW	18V XR FVA anglegrinder 125 mm TSTAK 1 X 6.0 Ah



UP TO 50% MORE POWER*

TAKE ADVANTAGE OF MORE POWER

XR BATTERY DCB184 5.0 AH



POWER OUTPUT 982 WATT

Power output by using 5.0 Ah battery

18V XR WITH FLEXVOLT ADVANTAGE



POWER OUTPUT 1475 WATT

Power output by using 6.0 Ah battery

XR FLEXVOLT BATTERY DCB546 6.0 AH



DCS386 - 18V XR RECIPROCATING SAW WITH FLEXVOLT ADVANTAGE

The DCS386 delivers up to 50% more power when paired with a DCB546 XR FLEXVOLT 6.0 Ah battery versus a DCB184 18V XR 5.0 Ah battery. The DCS386 has been equipped with a crank type drive train for smoother, more efficient operation and reduced vibration, and delivers an impressive no-load speed of 3,000 spm.

SPECIFICATIONS

Spænding	18 volt
Stroke length	29 mm
No load stroke rate	0 - 3000 spm
Max. Cutting capacity	Wood 300 mm / Metal 130 mm
Weight	3,5 kg

ART.NR.

PRODUCTDESCRIPTION

DCS386NT-XJ	18V XR FVA reciprocating saw TSTAK, bare unit
DCS386T1-QW	18V XR FVA reciprocating saw TSTAK 1 X 9.0 Ah



UP TO **77%**
MORE POWER*

TAKE ADVANTAGE OF MORE POWER

XR
BATTERY
DCB184
5.0 AH



POWER OUTPUT
975 WATT

Power output by using 5.0 Ah battery

18V XR WITH **FLEXVOLT** ADVANTAGE



POWER OUTPUT
1727 WATT

Power output by using 6.0 Ah battery

XR FLEXVOLT
BATTERY
DCB546
6.0 AH



DCS573 - 18V XR 190MM CIRCULAR SAW WITH FLEXVOLT ADVANTAGE

The DCS573 delivers up to 77% more power when paired with a DCB546 XR FLEXVOLT 6.0 Ah battery versus a DCB184 18V XR 5.0 Ah battery. With a 67 mm depth of cut, outstanding dust management features, tool-free depth adjustment and an electronic safety brake, this rugged circular saw can tackle tough applications such as rip and bevel cuts and hard timber cutting.

SPECIFICATIONS

Power	18 volt
Blade diameter	190 mm
Blade bore	30 mm
Max. Cutting capacity	67 mm @ 90° / 51 mm @ 45°
No load capacity	5500 rpm
Weight	3,7 kg

ART.NR. PRODUCTDESCRIPTION

DCS573NT-XJ	18V XR FVA circular saw 190 mm TSTAK, bare unit
DCS573T1-QW	18V XR FVA circular saw 190mm TSTAK 1 X 6.0 Ah

DEWALT®





18V XR PRODUCTS WITH FLEXVOLT ADVANTAGE

DEWALT 18V AND 54V BATTERY PLATFORM

18V XR



SELECTED PRODUCTS FROM 18V XR ASSORTMENT

- Cordless products to the professional craftman and industry.
- These products can be used with 18V and 18V/54V FLEXVOLT batteries.
- Meets the requirements of millions of professional users worldwide

XR FLEXVOLT ADVANTAGE



CURRENT 18V FLEXVOLT ADVANTAGE ASSORTMENT

- By using 18V/54V FLEXVOLT batteries instead of the traditional 18V XR batteries, increased performance (up to 1750 watt) can be reached.
- These products can be used with 18V XR and 18V/54V XR FLEXVOLT batteries.
- For heavy duty users requiring power and runtime.

54V XR FLEXVOLT



SELECTED PRODUCTS FROM 54V XR ASSORTMENT

- Our best in class cordless tools that replace corded tools.
- These products can be 54V/18V XR FLEXVOLT batteries.
- 54V technology delivers power levels that cannot be matched on 18V. For the most demanding users and applications.

POWER OUTPUT

UP TO
1000 WATT
DEWALT LARGEST CORDLESS SYSTEM

UP TO
1750 WATT
DEWALT MOST POWERFULL 18V TOOL

UP TO
3000 WATT
DEWALT BEST IN CLASS CORDLESS TOOLS THAT REPLACE CORDED TOOLS


POWER OUTPUT



**POWER OUTPUT
UP 1000 WATT
USING 18V XR
BATTERY
PLATFORM**



**TAKE
ADVANTAGE
OF MORE POWER
POWER OUTPUT
UP 1750 WATT
USING 54V/18V XR
BATTERY
PLATFORM**





18V XR BATTERY PLATFORM



DCB183



DCB187



DCB189



DCB182



DCB184



DCBP034



54V/18V XR BATTERY PLATFORM



DCB546



DCB547



DCB548



DCB549

www.DeWALT.com

The yellow and black colour scheme is used on DeWALT Power Tools and Accessories as a trademark. DeWALT cannot be held liable for any inaccuracies of description or illustration and reserve the right to change specifications without notification.

Be the first to see product news and special offers from DeWALT. Register at MyDeWALT

REGISTER AT

MY DeWALT®