

Pruning Saw LXT®

DUC150

18V, 8,0 m/s, 15 cm / 6"

Model DUC150 is a 150mm pruning saw powered by 18V LXT® Li-Ion battery

Easy-to-use, lightweight and compact product enables easy pruning of garden or orchard trees. The main features and benefits are: New tool-less change and tension adjustment of saw chain. Automatic chain lubrication. Lock-off lever accessible from both sides. Rear hand guard. Moveable guard. Saw chain: 80TXL.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	8,0 m/s
Chain Pitch	0,325 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	32
Chain Oil Tank	55 ml
Brushless Motor	✓
chain bar length	150 mm (6")
Vibration Level, Cutting Wood	4,8 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Power Level (L _{WA})	87 dB(A)
Sound Pressure Level (L _{pA})	79 dB(A)

User benefits

- Compact and lightweight design
- Brushless maintenance-free and long-life motor
- Electric brake for maximum productivity and increased operator safety
- Automatic chain lubrication
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Ergonomic soft grip handle provides increased comfort
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing