




Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Type: **Pin**

Number of Positions: **1**

Sealable: **No**

Contact Current Rating (Max): **60 A**

Circuit Application: **Power**

Features

Product Type Features

Sealable	No
----------	----

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Material	Beryllium Copper
--------------------------	------------------

Contact Features

Contact Type	Pin
Contact Current Rating (Max)	60 A

Usage Conditions

Operating Temperature Range	-196 – 200 °C[-321 – 392 °F]
-----------------------------	------------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	




Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-192042-5
LAIVS 0.15mm(.006) UNPL


Customers Also Bought



TE Part #643075-4
04P MTA100 MOLDED COVER



TE Part #33469
TERMINAL,SOLIS R 4 1/4




TE Part #3-643814-4
04P MTA100 CONN ASSY POL RIB



TE Part #4-192038-8
LA3,.250,.006,SILVER






TE Part #1-2176331-7
CRGP 2512 220R 1%



TE Part #770849-2
02P SL156 HSG W/LCK RMP & TABS



TE Part #1625854-1
1206 PROBE PAD



TE Part #8-192013-2
LA1A,.625,.006,SILVER PL



TE Part #2289297-7
M12 STRGT PLUG TO M12 STRGT
SOCKET AA

TE Part #GA10K3D1118
PRO2-10K OHMS +/- 1% @ 25°C

Documents

Product Drawings

BRIDGE FORMED BAND,(M) L-.32

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-192042-8_R.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-192042-8_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-192042-8_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English