



Connectors > Automotive Connectors > Connector Housings > HEAVY DUTY SEALED CONNECTOR HOUSINGS



Connector & Housing Type: **Housing for Male Terminals**

Mating Tab Width: **1.6 mm [.063 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **3**

Centerline (Pitch): **4 mm [.157 in]**

[All HEAVY DUTY SEALED CONNECTOR HOUSINGS \(190\)](#)

Features

Product Type Features

Connector & Housing Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	60 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 60 V

Body Features

Cable Exit Angle	180°, 90°
Body Material	PBT GF
Primary Product Color	Green



Connector Code	C
Contact Features	
Contact Size	1.6mm
Contact Type	Tab
Mating Tab Width	1.6 mm[.063 in]
Contact Current Rating (Max)	20 A
Mechanical Attachment	
Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount
Housing Features	
Centerline (Pitch)	4 mm[.157 in]
Dimensions	
Product Width	47.05 mm[1.852 in]
Product Length	37.5 mm[1.476 in]
Product Height	29.8 mm[1.173 in]
Usage Conditions	
Operating Temperature (Max)	70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Degree of Protection	IP67
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	450
Packaging Method	Carton



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2112289-1
PROTECTION CAP, GROUP A, ASSY



TE Part # 3-1418448-1
3POS AMP MCP1.5k REC.HSG CODC




TE Part # CAT-H3399-SL34
HEAVY DUTY CONNECTORS FIXING SLIDES



TE Part # 1670365-1
COVER MIXED, 180, 2-3POS, BK





TE Part # 964972-1
EINZELLEITERDICHUNG



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 1670365-2
COVER MIXED, 180, 2-3POS, NW4.5



TE Part # 3-1703843-2
3POS,TAB 1.6X0.6,TAB HSG,ASSY,



TE Part # 539651-2
MATRIZE MICRO TIMER



TE Part # 2-964269-2
TAB A 1.6x0.6 CONTACT CF SWS Ag

Also in the Series

Heavy Duty Sealed Connector Series



Automotive Connector Caps & Covers
(25)



Automotive Housings(197)



Automotive Seals & Cavity Plugs(5)



Data Connectivity Headers(2)



Data Connectivity Housings(18)



Other Automotive Connector
Accessories(22)


Customers Also Bought




TE Part #4-1703843-1
HEAVY DUTY SEALED CONNECTOR
HOUSINGS



TE Part #1670150-1
COVER MIXED,90,NW8.5



TE Part #1-929974-4
2,5MM SWS REC.CONT.



TE Part #1742633-1
TAB,.063 X .032,300 SERIES,MAG



Documents

Product Drawings

3POS,TAB 1.6X0.6,TAB HSG,ASSY,
English

CAD Files

Customer View Model
ENG_CVM_CVM_3-1703843-1_H.3d_stp.zip
English

Customer View Model
ENG_CVM_CVM_3-1703843-1_H.2d_dxf.zip
English

3D PDF
3D

Customer View Model
ENG_CVM_CVM_3-1703843-1_H.3d_igs.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HDSCS CAN Bus Y-Connector and 120 Resistor Brochure
English

HDSCS Catalog
English

ICT Terminals and Connectors Catalogue
English

CONNECTOR SELECTOR
English

Product Specifications

Application Specification
English

Product Environmental Compliance

Product Compliance
English

Product Compliance

3-1703843-1

Housing for Male Terminals, Wire-to-Wire, 3 Position, .157 in [4 mm] Centerline,
Sealable, Green, Signal, Heavy Duty Sealed Connector Series



English