



Pushing Performance
Since 1945

RJI MF-PN RJ45plug Cat5, 4p IDC straight




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1140
Specification	RJI MF-PN RJ45plug Cat5, 4p IDC straight
HARTING eCatalogue	https://harting.com/09451511140

Identification

Category	Connectors
Series of hoods/housings	HARTING RJ Industrial®
Element	Connector
Specification	PROFINET Multi Feature RJ45 Straight
Features	Suitable for all PoE versions

Version

Termination method	IDC insulation displacement termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4

Technical characteristics

Conductor cross-section	0.12 ... 0.32 mm² Stranded 0.12 ... 0.32 mm² Solid
Conductor cross-section [AWG]	AWG 26/7 ... AWG 22/7 Stranded AWG 26/1 ... AWG 22/1 Solid
Wire outer diameter	0.8 ... 1.6 mm
Rated current	1.76 A
Rated voltage	50 V AC 60 V DC
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s



Pushing Performance
Since 1945

Technical characteristics

Insulation resistance	$> 5 \times 10^9 \Omega$
Contact resistance	$\leq 20 \text{ m}\Omega$
Contact resistance, shielding	$\leq 100 \text{ m}\Omega$
Limiting temperature	$-40 \dots +85 \text{ }^\circ\text{C}$
Relative humidity	95 % Non-condensing (operation)
Insertion force	$\leq 25 \text{ N}$
Withdrawal force	$\leq 25 \text{ N}$
Mating cycles	≥ 750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm
Test voltage U_{DC}	1 kV (contact-contact) 1.5 kV (contact-ground)
Vibration resistance	10-500 Hz, 0.35 mm / 50 m/s ² , 2h/axis 5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	50 g / 30 ms, 3 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (insert)	Polycarbonate (PC)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Colour (hood/housing)	silver
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 60603-7 Mating face
	ISO/IEC 11801
	EN 50173-1
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	0.002 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140224308
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408