

SAFETY DATA SHEET RESIN REMOVER SOLVENT

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name RESIN REMOVER SOLVENT
Product No. RRS-b, ERRS05L, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK WENTWORTH LTD
ASHBY PARK, COALFIELD WAY,
ASHBY DE LA ZOUCH, LEICESTERSHIRE
LE65 1JR
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm GMT Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Flam. Liq. 2 - H225
Human health	EUH066; Eye Irrit. 2 - H319; STOT SE 3 - H336
Environment	Not classified.

Classification (1999/45/EEC)

Xi; R36. F; R11. R66, R67.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Label In Accordance With (EC) No. 1272/2008



Signal Word

Danger

Hazard Statements

H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

RESIN REMOVER SOLVENT

Precautionary Statements

P280	Wear protective gloves, eye and face protection.
Supplementary Precautionary Statements	
P210	Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P271	Use only outdoors or in a well-ventilated area.
P261	Avoid breathing vapour/spray.
P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a POISON CENTER or doctor/physician if you feel unwell.
P312	Get medical advice/attention.
P313	
Supplemental label information	
EUH066	Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

BUTANONE	30-60%	
CAS-No.: 78-93-3	EC No.: 201-159-0	Registration Number: 01-2119457290-43
Classification (EC 1272/2008) Flam. Liq. 2 - H225 EUH066 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R66 R67	
ACETONE	5-10%	
CAS-No.: 67-64-1	EC No.: 200-662-2	
Classification (EC 1272/2008) Flam. Liq. 2 - H225 EUH066 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R66 R67	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

Ingestion

DO NOT INDUCE VOMITING! Provide fresh air, warmth and rest, preferably in comfortable upright sitting position. Rinse mouth thoroughly. Get medical attention.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

RESIN REMOVER SOLVENT

4.3. Indication of any immediate medical attention and special treatment needed

Treat Symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Use: Alcohol resistant foam. Powder. Dry chemicals, sand, dolomite etc.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

5.3. Advice for firefighters

Special Fire Fighting Procedures

Move container from fire area if it can be done without risk. Use water to keep fire exposed containers cool and disperse vapours.

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers. Wear necessary protective equipment.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. Collect and dispose of spillage as indicated in section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

Storage Class

Flammable liquid storage.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
ACETONE	WEL	500 ppm	1210 mg/m ³	1500 ppm	3620 mg/m ³	
BUTANONE	WEL	200 ppm	600 mg/m ³	300 ppm	899 mg/m ³	Sk

RESIN REMOVER SOLVENT

WEL = Workplace Exposure Limit.
Sk = Can be absorbed through skin.

ACETONE (CAS: 67-64-1)

DNEL

Industry	Dermal	Long Term	Systemic Effects	186 mg/kg/day
Industry	Inhalation.	Long Term	Systemic Effects	1210 mg/m3
Industry	Inhalation.	Short Term	Local Effects	2420 mg/m3
Consumer	Dermal	Long Term	Systemic Effects	62 mg/kg/day
Consumer	Inhalation.	Long Term	Systemic Effects	200 mg/m3

PNEC

Freshwater	10.6	mg/l
Marinewater	1.06	mg/l
Intermittent release	21	mg/l
STP	100	mg/l
Sediment (Freshwater)	30.4	mg/kg
Sediment (Marinewater)	3.04	mg/kg
Soil	29.5	mg/kg

BUTANONE (CAS: 78-93-3)

DNEL

Industry	Dermal	Long Term	1161	mg/kg/day
Industry	Inhalation.	Long Term	600	mg/m3
Consumer	Dermal	412	mg/kg/day	
Inhalation.	106	mg/m3		
Oral	31	mg/kg/day		

PNEC

Freshwater	55.8	mg/l
Marinewater	55.8	mg/l
STP	709	mg/l
Sediment	284.7	mg/kg
Soil	22.5	mg/kg

8.2. Exposure controls

Protective equipment



Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

Respiratory equipment

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment. Use respiratory equipment with combination filter, type A2/P3. EN14387

Hand protection

Use protective gloves. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Nitrile gloves are recommended. Gloves should conform to EN374

Eye protection

Wear approved chemical safety goggles where eye exposure is reasonably probable. EN166

Other Protection

Wear suitable protective clothing as protection against splashing or contamination.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Colourless.
Odour	Characteristic.
Flash point (°C)	-17 (1.4 F) CC (Closed cup).

RESIN REMOVER SOLVENT

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not determined.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition.

10.5. Incompatible materials

Materials To Avoid

Strong oxidising substances.

10.6. Hazardous decomposition products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Inhalation

May cause irritation to the respiratory system.

Ingestion

May cause stomach pain or vomiting.

Skin contact

Product has a defatting effect on skin. Prolonged or repeated exposure may cause severe irritation.

Eye contact

Irritating to eyes.

Toxicological information on ingredients.

ACETONE (CAS: 67-64-1)

Acute toxicity:

Acute Toxicity (Oral LD50)

5800 mg/kg Rat

Acute Toxicity (Dermal LD50)

15800 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

76 mg/l (vapours) Rat 4 hours

RESIN REMOVER SOLVENT

BUTANONE (CAS: 78-93-3)

Toxic Dose 1 - LD 50

>2193 mg/kg (oral rat)

Acute toxicity:

Acute Toxicity (Oral LD50)

> 2193 mg/kg Rat

Acute Toxicity (Dermal LD50)

> 5000 mg/kg Rabbit

Aspiration hazard:

Inhalation

Vapour may irritate respiratory system or lungs. Vapours may cause drowsiness and dizziness.

Ingestion

May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.

Skin contact

Irritating to skin. Repeated exposure may cause skin dryness or cracking.

Irritating to eyes.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment.

12.1. Toxicity

Ecological information on ingredients.

ACETONE (CAS: 67-64-1)

Acute Toxicity - Fish

LC50 96 hours 5540 mg/l Onchorhynchus mykiss (Rainbow trout)

LC50 96 hours 11000 mg/l Freshwater fish

Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 12600 mg/l Daphnia magna

Acute Toxicity - Aquatic Plants

NOEC 96 hours 430 mg/l Freshwater algae

BUTANONE (CAS: 78-93-3)

Acute Fish Toxicity

Not considered toxic to fish.

LC 50, 96 Hrs, Fish mg/l

3200 - 5600

EC 50, 48 Hrs, Daphnia, mg/l

7060

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

Ecological information on ingredients.

ACETONE (CAS: 67-64-1)

Degradability

The product is easily biodegradable.

BUTANONE (CAS: 78-93-3)

Degradability

The product is easily biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

RESIN REMOVER SOLVENT

Ecological information on ingredients.

BUTANONE (CAS: 78-93-3)

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

Ecological information on ingredients.

BUTANONE (CAS: 78-93-3)

Mobility:

The product is soluble in water.

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

Ecological information on ingredients.

BUTANONE (CAS: 78-93-3)

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

Ecological information on ingredients.

BUTANONE (CAS: 78-93-3)

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

14.1. UN number

UN No. (ADR/RID/ADN)	1993
UN No. (IMDG)	1993
UN No. (ICAO)	1993

14.2. UN proper shipping name

Proper Shipping Name FLAMMABLE LIQUID, N.O.S. (1, 3-DIOXOLANE, BUTANONE)

14.3. Transport hazard class(es)

ADR/RID/ADN Class	3
ADR/RID/ADN Class	Class 3: Flammable liquids.
ADR Label No.	3
IMDG Class	3
ICAO Class/Division	3
Transport Labels	

RESIN REMOVER SOLVENT



14.4. Packing group

ADR/RID/ADN Packing group	II
IMDG Packing group	II
ICAO Packing group	II

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant
No.

14.6. Special precautions for user

EMS	F-E, S-E
Emergency Action Code	•3YE
Hazard No. (ADR)	33
Tunnel Restriction Code	(D/E)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No information required.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Issued By	Helen O'Reilly
Revision Date	APRIL 2013
Revision	2

RESIN REMOVER SOLVENT

SDS No. 13126

Risk Phrases In Full

R11 Highly flammable
R36 Irritating to eyes.
R66 Repeated exposure may cause skin dryness or cracking.
R67 Vapours may cause drowsiness and dizziness.

Hazard Statements In Full

EUH066 Repeated exposure may cause skin dryness or cracking.
H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.