



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **18**

Number of Rows: **2**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Applied Pressure                  | Standard              |
| PCB Connector Type                | PCB Mount Receptacle  |
| Connector System                  | Board-to-Board        |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |
| Connector Product Type            | Connector Assembly    |

Configuration Features

|                              |          |
|------------------------------|----------|
| Board-to-Board Configuration | Parallel |
| Stackable                    | Yes      |
| PCB Mount Orientation        | Vertical |
| Number of Positions          | 18       |
| Number of Rows               | 2        |

Electrical Characteristics

|                       |         |
|-----------------------|---------|
| Operating Voltage     | 333 VAC |
| Insulation Resistance | 5000 MΩ |

Body Features

|                       |          |
|-----------------------|----------|
| Connector Profile     | Standard |
| Primary Product Color | Black    |



Contact Features

|                                                |                      |
|------------------------------------------------|----------------------|
| Contact Mating Area Plating Material Thickness | .762 μm[30 μin]      |
| Mating Square Post Dimension                   | .64 mm[.025 in]      |
|                                                | 150 μin              |
| Contact Shape & Form                           | Square               |
| Contact Protection Type                        | Closed Entry Housing |
| Contact Base Material                          | Phosphor Bronze      |
| PCB Contact Termination Area Plating Material  | Tin-Lead             |
| Contact Mating Area Plating Material           | Gold (Au)            |
| Contact Type                                   | Socket               |
| Contact Current Rating (Max)                   | 2 A                  |

Termination Features

|                                               |                       |
|-----------------------------------------------|-----------------------|
| Rectangular Termination Post & Tail Width     | .69 mm[.027 in]       |
| Rectangular Termination Post & Tail Thickness | .2 mm[.008 in]        |
| Termination Post & Tail Length                | 2.92 mm[.115 in]      |
| Termination Method to PCB                     | Through Hole - Solder |

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| PCB Mount Retention     | Without     |
| PCB Mount Alignment     | Without     |
| Connector Mounting Type | Board Mount |
| Mating Alignment        | Without     |

Housing Features

|                       |                |
|-----------------------|----------------|
| Mating Entry Location | Top            |
| Housing Material      | Polyester - GF |
| Centerline (Pitch)    | 2.54 mm[.1 in] |

Dimensions

|                             |                         |
|-----------------------------|-------------------------|
| Row-to-Row Spacing          | 2.54 mm[.1 in]          |
| Stack Height                | 10.92 mm[.43 in]        |
| PCB Thickness (Recommended) | 1.57 mm[.055 – .094 in] |
| Connector Height            | 5.03 mm[.198 in]        |

Usage Conditions

|                            |          |
|----------------------------|----------|
| Housing Temperature Rating | Standard |
|----------------------------|----------|



Operating Temperature Range

-65 – 105 °C[-85 – 221 °F]

Operation/Application

|                        |                |
|------------------------|----------------|
| Solder Process Feature | Board Standoff |
| Circuit Application    | Signal         |

Industry Standards

|                                             |                       |
|---------------------------------------------|-----------------------|
| Compatible With Approved Standards Products | CSA LR7189, UL E28476 |
| UL Flammability Rating                      | UL 94V-0              |

Packaging Features

|                    |           |
|--------------------|-----------|
| Packaging Quantity | 28        |
| Packaging Method   | Box, Tube |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                              |
|-----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Not Compliant                                                                                                                                                                                                                                                                                                                                                                                                                |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2024 (241)<br>SVHC > Threshold:<br>Pb (13% in Component Part)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                                                                                                                                                                                                                                                                                                               |
| Solder Process Capability                     | Wave solder capable to 240°C                                                                                                                                                                                                                                                                                                                                                                                                 |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts




TE Part # 86286-1  
KEYING PLUG


Also in the Series | Modu Connector System




Board-to-Board Headers & Receptacles(814)



Board-to-Board Jumpers & Shunts(5)




Connector Hardware(4)




PCB Headers & Receptacles(814)

Customers Also Bought



TE Part #111620-1  
2MM KEYING PLUG,COMB OF 10



TE Part #5-2176397-7  
3502 220R 1%



TE Part #2-640457-0  
20P MTA100 HDR ASSY SQ R/A F/L



TE Part #826925-9  
9P MOD2 STIFT LEI



TE Part #1-1478923-0  
SMA R/A PLG S/CRMP RG58 GSS



TE Part #2-2176049-1  
RLP73N 1E R36 1% 1K RL



TE Part #1-826942-6  
16P MOD2 STIFT LEI



TE Part #6-146253-5  
30 MODII HDR DRST B/A .100CL LF



Documents

Product Drawings

[18 MODII VRT DR CE 100/115](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_534206-9\\_N.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_534206-9\\_N.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_534206-9\\_N.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English