

Features

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material: Brass Nickel-Plated Finish
- Single Shut Off (One side is with valve)
- Euro Profile
- DN7.2
- Flow 1000 l/min
- Compatible with:
TST SWING COUPLING C
TST 025
PARKER - RECTUS 25
CEJN 320
JWL 520, 530
PARKER PE

RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 0325612



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Series 26 Quick Connect Couplings


Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material: Brass Nickel-Plated Finish
- Single Shut Off (One side is with valve)
- Euro Profile
- DN7.2
- Flow 1000 l/min
- Compatible with:
TST SWING COUPLING C
TST 025
PARKER - RECTUS 25
CEJN 320
JWL 520, 530
PARKER PE


Specifications

Manufacturer Series	026
Coupling Type	Quick Connect Coupling Plug
Connection Standard	DN 7.2 Euro Profile
Connection Standard Compatible With	TST 025; PARKER RECTUS 25, CEJN 320; JWL 520 & 530; PARKER PE
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C
Maximum Operating Pressure	35bar
Flow	1000 l/min
Flow Direction & Sealing	Through Type Coupling
Material	Brass
Finish	Nickel Plated
Connection Type	Threaded
Thread Size	1/2 in
Thread Standard	G
Thread Gender	Male
Coupling Gender	Male
Threaded Connection	G 1/2 Male
Seal material	N/A
Hose Barb Connection	N/A

Specifications



Dimensions (mm)		
SW	L	ØD
22	36	-





Material Code

A = Brass Nickel Plated


B = Brass Nickel Plated

C = Brass Nickel Plated

S = Brass Nickel Plated



Plug Profile Serie 026



Series 26 Quick Connect Couplings




0 - 35 bar
(0-508 PSI)



-20° to +100°C (NBR)
-4° to +212°F

Shut Off
Type



OM 262 - 00990
OM 200 - 00650

FLOW

1000 lt/min

DN

7.2 mm