



SPEED **SENSORS**

Product Range Guide

Honeywell

FOR INNOVATION THAT’S WELL APART, THERE’S ONLY HONEYWELL.

With more than 50,000 products ranging from snap-action, limit, toggle, and pressure switches to position, speed, pressure, and airflow sensors, Honeywell has one of the broadest sensing and switching portfolios.

Honeywell sensor, switch, and control components are tailored to exact specifications for stronger performance, longer productivity, and increased safety. Enhanced accuracy and durability are built into every part, improving output and endurance. For our customers, this can reduce expenditures and operational costs. Our global footprint and channels help to competitively price such components for your chosen application and provide immediate technical support.

While Honeywell’s switch and sensor solutions are suitable for a wide array of basic and complex applications, our custom-engineered solutions offer enhanced precision, repeatability, and ruggedness. We offer domain knowledge and technology resources, along with a close working relationship, to develop and deliver cost-effective, individually tailored solutions. Whether clean-slate development or simple modifications to an existing design are needed, our expertly engineered solutions help to meet the most stringent requirements with world-class product designs, technology integration, and customer-specific manufacturing.

Global service, sourcing, and manufacturing. Industry-leading engineers. Value-added assemblies and solutions. A one-stop, full-service, globally competitive supplier.

TABLE OF CONTENTS	
Anisotropic Magnetoresistive Sensor ICs	3
Hall-effect Digital Sensor ICs	4-5
Hall-effect Digital and Linear Sensor ICs	6
Value-Added Magnetic Sensors	7-8
Active Speed Sensors	9-10
Passive Speed Sensors	11



MAGNETIC SENSORS MAGNETO- RESISTIVE SENSOR ICs



With a built-in magnetoresistive bridge integrated on silicon and encapsulated in a plastic package, magnetoresistive sensor ICs feature an integrated circuit that responds to low fields at large distances. Potential applications include laptops, material handling equipment, pneumatic cylinders, and battery-powered equipment including hand-held scanners, computers, and water/gas/electricity meters.

	NANOPOWER SERIES	STANDARD POWER SERIES	2SS52M SERIES	VF401	APS00B
Description	Omnipolar MR Sensor IC	Omnipolar MR Sensor IC	Omnipolar MR Digital sensor IC	2-wire MR fine pitch ring magnet sensor IC	High resolution magnetic displacement sensor IC
Magnetic actuation type	Omnipolar	Omnipolar	Omnipolar	Differential bridge	Analog, saturated mode
Package style¹	SOT-23	SM351RT, SM353RT: SOT-23 SM451RT, SM453RT: flat TO-92-style	SS552MT: SOT-89B All others: Leaded U-Pack in bulk or ammopack	VF-401 flat TO-92-style	SOIC-8
Supply voltage range	1.65 Vdc to 5.5 Vdc	3 Vdc to 24 Vdc	3.8 Vdc to 30 Vdc	4.5 Vdc to 16 Vdc	1 Vdc to 12 Vdc
Supply current	SM351LT: 360 nA typ. SM353LT: 310 nA typ.	8 mA max.	11 mA max	Operate: 16.8 mA max. Release: 8.4 mA max.	7 mA max.
Output type	Low: 0.03 V typ. High: Vs -0.03 V typ.	Digital sinking	Digital sinking	Digital sourcing	sin(2Θ), cos(2Θ)
Operating temperature range	-40°C to 85°C [-40°F to 185°F]	-40°C to 85°C [-40°F to 185°F]	-40°C to 150°C [-40°F to 302°F]	-40°C to 150°C [-40°F to 302°F]	-40°C to 150°C [-40°F to 302°F]
Features	High sensitivity: SM351LT: 7 Gauss typ., 11 Gauss max. SM353LT: 14 Gauss typ., 20 Gauss max. Designed to accommodate applications with large air gaps, small magnetic fields and low power requirements	Ultra-high sensitivity: SM351RT, SM451R: 7 Gauss typ., 11 Gauss max. Very high sensitivity: SM353RT, SM453R: 14 Gauss typ., 20 Gauss max.	Omnipolar magnetics, sinking output, low Gauss operation (25 G max.), operating speed of 0 kHz to over 100 kHz	Wide speed capability, output pattern independent of gap between target and sensor, improved insensitivity to run-out, tilt, and twist, reverse polarity protection	Dual analog voltages respond to changes in magnetic field angle; sine and cosine output; accurate to 0,102 mm [0.004 in]

¹Dimensions:
• SOT-23: 2,8 mm x 2,9 mm [0.11 in x 0.11 in]
• Flat TO-92-style: 3,0 mm x 4,0 mm [0.12 in x 0.16 in] (not including leads)
• VF-401 flat TO-92-style: 3,0 mm x 4,06 mm [0.12 in x 0.16 in] (not including leads)
• SOT-89B: 4,2 mm x 4,5 mm [0.16 in x 0.18 in]
• U-Pack: 4,5 mm x 4,5 mm [0.18 in x 0.18 in] (not including leads)
• SOIC-8: 4,9 mm x 6,0 mm [0.19 in x 0.24 in]

MAGNETIC SENSORS
HALL-EFFECT DIGITAL SENSOR ICS

Constructed from a thin sheet of conductive material with output connections perpendicular to the direction of current flow. Include bipolar, latching, omnipolar, or unipolar magnetics in a variety of package styles. Energy-efficient micropower versions for potential applications with low power requirements and/or battery operation.

									
	SL353	SS30AT, SS40A, SS50AT	SS311PT, SS411P	SS340RT, SS440R SERIES	SS345PT, SS445P	SS351AT, SS451A, SS551AT	SS360NT, SS360ST, SS360ST-10K, SS460S, SS460S-T2	VF360NT, VF360ST, VF460S	SS360PT, SS460P, SS460P-T2
Description	Micropower omnipolar Hall-effect digital sensor IC	Low-cost bipolar Hall-effect digital sensor IC	Low-cost bipolar Hall-effect digital sensor IC with built-in pull-up resistor	Low-cost unipolar Hall-effect digital sensor IC	Unipolar Hall-effect digital sensor IC with built-in pull-up resistor	Low-cost omnipolar Hall-effect digital sensor IC	High sensitivity, latching Hall-effect digital sensor IC	High sensitivity, latching Hall-effect digital sensor IC	High sensitivity latching digital Hall-effect sensor IC with built-in pull-up resistor
Magnetic actuation type	Omnipolar	Bipolar	Bipolar	Unipolar	Unipolar	Omnipolar	Latching	Latching	Latching
Package style and packaging ¹	SOT-23 (pocket tape and reel)	SS30AT: SOT-23 (pocket tape and reel) SS40A: flat TO-92-style (bulk) SS50AT: SOT-89B (pocket tape and reel)	SS311PT: SOT-23 (pocket tape and reel) SS411P: flat TO-92-style (bulk)	SS340RT: SOT-23 (pocket tape and reel) SS440R: flat TO-92-style	SS345PT: SOT-23 (pocket tape and reel) SS445P: flat TO-92-style (bulk)	SS351AT: SOT-23 (pocket tape and reel) SS451A: flat TO-92-style (bulk) SS551AT: SOT-89B (pocket tape and reel)	SS360NT, SS360ST, SS360ST-10K: SOT-23 (pocket tape and reel) SS460S: flat TO-92-style (bulk) SS460S-T2: flat TO-92-style, formed leads (ammopack)	VF360NT, VF360ST: SOT-23 (pocket tape and reel) VF460S: flat TO-92-style (bulk)	SS360PT: SOT-23 (pocket tape and reel) SS460P: flat TO-92-style (bulk) SS460P-T2: flat TO-92-style, formed leads (ammopack)
Supply voltage	2.2 Vdc to 5.5 Vdc	4.5 Vdc to 24 Vdc	2.7 Vdc to 7 Vdc	SS340RT >125°C [247°F]: 3 Vdc to 12 Vdc all others: 3 Vdc to 18 Vdc	2.7 Vdc to 7.0 Vdc	SS351AT, SS551AT (-40°C to 125°C [-40°F to 257°F]): 3 Vdc to 24 Vdc SS351AT (150°C [302°F]): 3 Vdc to 12 Vdc SS451A (-40°C to 150°C [-40°F to 302°F]): 3 Vdc to 24 Vdc	3 Vdc to 24 Vdc	3 Vdc to 24 Vdc	3 Vdc to 24 Vdc
Supply current	SL353LT: 1.8 m typ. at 2.8 Vdc SL353HT: 0.33 mA typ. at 2.8 Vdc	10 mA max.	14 mA max.	8 mA	14 mA	3 V: 5 mA max. at 25°C [77°F] 5 V: 6 mA max. at 25°C [77°F]	8 mA max.	8 mA	10 mA
Operating temperature range	-40°C to 85°C [-40°F to 185°F]	SS40A: -40°C to 125°C [-40°F to 257°F] SS30AT, SS50AT: -40°C to 125°C [-40°F to 257°F]	-40°C to 150°C [-40°F to 302°F]	SS340RT (3 Vdc to 24 Vdc): -40°C to 125°C [-40°F to 257°F] SS340RT (3 Vdc to 12 Vdc), SS440R (3 Vdc to 24 Vdc): -40°C to 150°C [-40°C to 302°F]	-40°C to 150°C [-40°F to 302°F]	-40°C to 150°C [-40°F to 302°F]	-40°C to 125°C [-40°F to 257°F]	-40°C to 150°C [-40°F to 302°F]	-40°C to 125°C [-40°F to 257°F]
Features	Low supply voltage combined with very low average current reduces power consumption	High output current and speed capability, reverse polarity protection	Built-in pull-up resistor, low voltage, enhanced sensitivity	Simple activation from a North pole (SS340RT) or South pole (SS440R), multiple magnetic sensitivities (high, medium, and low)	Simple activation from a North pole (SS345PT) or a South pole (SS445P)	Built-in reverse polarity protection, typical operating point of 85 G at 25°C [77°F]	Fastest response time in its class, no chopper stabilization	Qualified to the AEC-Q100 standard for potential use in automotive applications, fastest response time in its class	Fastest response time in its class, no chopper stabilization, operates from only 30 Gauss typical, at 25°C [77°F]



¹Dimensions:
• SOT-23: 2,8 mm x 2,9 mm [0.11 in x 0.11 in]
• Flat TO-92-style: 3,0 mm x 4,0 mm [0.12 in x 0.16 in] (not including leads)
• SOT-89B: 4,2 mm x 4,5 mm [0.16 in x 0.18 in]

MAGNETIC SENSORS
HALL-EFFECT
DIGITAL AND
LINEAR
SENSOR ICS

Potential applications are many, including closure detection; presence-absence, metering, and displacement sensing in laptops, drug carts, and battery-powered equipment including hand-held scanners, computers, and water/gas/electricity meters; and speed and RPM sensing in brushless dc motors.



DIGITAL	VF526DT
Description	Latching dual Hall-effect digital sensor IC with speed and direction outputs
Magnetic actuation type	Latching
Package style ¹	SOT-89B (pocket tape and reel)
Supply voltage	3.4 Vdc to 24 Vdc
Supply current	14 mA max.
Output type	Digital sinking
Operating temperature range	-40°C to 125°C [-40°F to 257°F]
Features	Latching magnetics, sinking output, tape and reel available





LINEAR	SS490 SERIES	SS39ET, SS49E, SS49E-F, SS49E-L, SS49E-T2, SS49E-T3, SS59ET
Description	Hall-effect linear sensor IC	Hall-effect linear sensor IC
Magnetic actuation type	Linear	Linear
Package style ¹	Flat TO-92-style, surface mount (pocket tape and reel) Flat TO-92-style, standard straight leads (bulk) Flat TO-92-style, formed leads (ammopack) Flat TO-92-style, standard straight leads (ammopack)	SS39ET: SOT-23 (pocket tape and reel) SS49E: Flat TO-92-style, standard straight leads (bulk) SS49E-F: Flat TO-92-style, formed leads (bulk) SS49E-L: Flat TO-92-style, long straight leads (bulk) SS49E-T2: Flat TO-92-style, formed leads (ammopack) SS49E-T3: Flat TO-92-style, standard straight leads (ammopack) SS59ET: SOT-89B (pocket tape and reel)
Supply voltage	4.5 Vdc to 10.5 Vdc	2.7 Vdc to 6.5 Vdc
Supply current	10 mA	10 mA max.
Output type	Ratiometric sinking or sourcing	Ratiometric sourcing
Operating temperature range	-40°C to 150°C [-40°F to 302°F]	-40°C to 100°C [-40°F to 212°F]
Features	Linear magnetics, ratiometric sourcing output, positive temperature coefficient, different package styles	Linear magnetics, ratiometric sourcing output, low voltage operation, different package styles

¹Dimensions:
• 4-Pin SIP: 3,6 mm x 5,1 mm [0.14 in x 0.20 in]
• SOT-89B: 4,2 mm x 4,5 mm [0.16 in x 0.18 in]
• Flat TO-92-style: 3,0 mm x 4,0 mm [0.12 in x 0.16 in] (not including leads)

MAGNETIC SENSORS
VALUE
ADDED


Consist of Hall-effect or magnetoresistive sensor ICs packaged in plastic housings for use in corrosive environments, or aluminum housings for non-corrosive use. Include digital or linear position sensors (activated by an external magnet) and vane sensors (activated by a ferrous metal actuator). Choice of cable materials provides application flexibility.



	103SR SERIES (DIGITAL)	103SR SERIES (LINEAR)
Description	Hall-effect digital position sensor	Hall-effect linear position sensor
Package material and style	Aluminum threaded barrel	Aluminum threaded barrel
Magnetic actuation type	Unipolar, bipolar, latching	Linear
Operation	Proximity to external magnet	Proximity to external magnet
Supply voltage range	4.5 Vdc to 24 Vdc	4.5 Vdc to 10.5 Vdc
Supply current	4 mA to 10 mA (inclusive)	7 mA
Output type	Digital sinking	Ratiometric sinking/sourcing
Operating temperature range	-40°C to 100°C [-40°F to 212°F]	-40°C to 100°C [-40°F to 212°F]
Dimensions	Ø11,9 mm x 25,4 mm [Ø15/32-2 x 1.0 in]	Ø11,9 mm x 25,4 mm [Ø15/32-2 x 1.0 in]
Features	Unipolar, bipolar, and latching magnetics, sinking or sourcing output, aluminum housing, color-coded jacketed cable, adjustable mounting	Linear magnetics, ratiometric sinking/sourcing output, aluminum housing, color-coded jacketed cable, adjustable mounting

MAGNETIC
SENSORS
VALUE
ADDED

Potential applications include position and RPM sensing, cam and crankshaft speed and position, transmissions, tachometers, traction control, and sprocket speed in fitness and information technology, food and beverage environments, chemical plants, and refineries.



	SR16/SR17 SERIES	SR3 SERIES	SR4 SERIES
Description	Low-cost Hall-effect vane sensor	Hall-effect digital position sensor	Magnetoresistive digital position sensor
Package material and style	SR16: Plastic dual tower with variety of terminations SR17: Plastic side-mount wire exit	Plastic threaded barrel	Plastic threaded barrel
Magnetic actuation type	–	Unipolar, bipolar	Omnipolar
Operation	Ferrous metal actuator	Proximity to external magnet	Proximity to external magnet
Supply voltage range	3.8 Vdc to 30 Vdc	4.5 Vdc to 24 Vdc	3.8 Vdc to 30 Vdc
Supply current	10 mA max.	10 mA	11 mA
Output type	Digital sinking	digital sinking	Digital sinking
Operating temperature range	-20°C to 85°C [-4°F to 185°F]	-40°C to 85°C [-40°F to 185°F]	-40°C to 85°C [-40°F to 185°F]
Dimensions	24,6 mm x 12,4 mm [0.97 in x 0.49 in]	Ø12,4 mm x 25,4 mm [Ø0.49 in x 1.0 in]	19,0 mm H x 25,4 mm [0.75 in H x 1.0 in]
Features	Sinking output, non-contact position sensing, environmentally sealed, three terminations	NEMA 3, 3R, 3S, 4, 4X, 12, and 13, unipolar and bipolar magnetics,sinking output, frequencies exceeding 100 Hz	NEMA 3, 3R, 3S, 4, 4X, 12, and 13, omnipolar magnetics, sinking output

SPEED
SENSORS
ACTIVE

Use multiple technologies to detect a change in a rotating, ferrous metal target such as a gear, shaft or similar mechanism to create an electronic signal for control system interface. No moving parts – speed and direction sensing, or speed sensing only, is accomplished without contacting the target. Dual or single digital output versions available.



	SNG-Q SERIES	SNDH-T SERIES	SNDH-H SERIES
Description	Quadrature speed and direction sensor with 4-wire output	Quadrature speed and direction sensor with 4-wire output	Single Hall-effect speed sensor
Housing	PBT	Stainless steel, plastic	Stainless steel, plastic
Supply voltage range	4.5 V to 26 V	4.5 Vdc to 18 Vdc	4 Vdc to 24 Vdc, 4.5 Vdc to 24 Vdc, 6.5 Vdc to 24 Vdc
Supply current	2 mA normal, 18 mA max.	18 mA max.	6 mA max., 14 mA max., 20 mA max.
Output type	Square wave	Square wave	Digital sinking
Operating frequency range	3 Hz to 20 kHz	1 Hz to 15 kHz	0 Hz to 12 kHz, 0 Hz to 15 kHz, 2 Hz to 15 kHz
Operating temperature range	-40°C to 150°C [-40°F to 302°F]	-40°C to 150°C [-40°F to 302°F]	-40°C to 150°C [-40°F to 302°F] (inclusive)
Dimensions	Ø15 mm x 35 mm L [Ø0.59 in x 1.38 in L] Ø15 mm x 45 mm L [Ø0.59 in x 1.77 in L]	Ø15 mm x 45 mm L [0.6 in x 1.77 in L]	Various, depends upon individual catalog listing
Features	Design and manufacturing platform-based approach enables cost-competitiveness and mechanical and electrical configurability; designed for potential applications where enhanced accuracy is required to detect small target features	Advanced performance dynamic offset self-calibration, short circuit and reverse voltage protection, low jitter output, near zero speed	Rotationally insensitive versions available, zero speed sensing versions available, range of connector options

SPEED
SENSORS
ACTIVE

Provide true zero speed capability and precise switch point measurement. Speed sensor diagnostics provide information on air gap and sensor failure for increased reliability and functionality. Potential applications include cam/crank shafts, transmissions, tachometers, traction control, dynamometers, process control, and factory automation.



	LCZ SERIES	ZH10 SERIES
Description	Single Hall-effect zero speed sensor	Single Hall-effect zero speed sensor
Housing	Stainless steel	Aluminum
Supply voltage range	4.5 Vdc to 26 Vdc	4 Vdc to 24 Vdc
Supply current	20 mA	6 mA
Output type	Digital sinking	Digital sinking
Operating frequency range	0 Hz to 15 kHz	0 Hz to 15 kHz
Operating temperature range	-40°C to 125°C [-40°F to 257°F]	-40°C to 125°C [-40°F to 257°F]
Dimensions	Ø9,5 mm [3/8 in/0.375 in] and Ø15,9 mm [5/8 in/0.625 in], 50,8 mm [2.00 in] and 76,2 mm [3.00 in] lengths	Ø11,9 mm x 25,4 mm L [Ø15/32 in x 1.0 in L]
Features	Omni-directional sensor to target, low power consumption, zero speed, digital output	Omni-directional sensor to target, low power consumption, zero speed, digital output



	584XX SERIES
Description	Digital magnetic speed sensor
Housing diameter	3/8, in 5/8 in; various lengths
Supply voltage	5 Vdc to 30 Vdc
Output signal	Digital square wave
Output voltage range	Low: 350 mV max. at 20 mA max. current sink High: (R _L x V _s) / (R _L + 2.2 kOhm)
Operating frequency (max.)	10 kHz, 50 kHz
Housing material/style	Stainless steel/threaded
Termination	MS3106A-10SL-3S (5/8 only) or prelead
Vibration	Meets MIL-STD 202F, method 204D
Operating temperature range	-40°C to 107°C [-40°F to 225°F]
Features	Produces constant amplitude output signals suitable for direct use in many digital and logic control applications, internal digital signal conditioning

SPEED
SENSORS
PASSIVE

Passive Variable Reluctance Sensors (VRS) deliver direct conversion of actuator speed to an analog frequency. Transportation applications include engine, transmission, and wheel speed sensing. Industrial applications include electric motor speed, plant floor machinery, and pump RPM.



	VRS GENERAL PURPOSE	VRS HAZARDOUS LOCATION	VRS HIGH OUTPUT
Description/potential applications	Used where medium to high speeds or in electrically noisy environments with relatively small air gaps exist	Used where explosion-proof or intrinsically safe sensors are required	Used where higher output voltages are needed, perform best at low to medium speeds with medium to high impedance loads (sealed front-end versions for use where the sensor is exposed to fluids, lubricants or adverse environmental conditions)
Output voltage range	8 Vp-p to 40 Vp-p (Inclusive)	30 Vp-p to 60 Vp-p (Inclusive)	8 Vp-p to 190 Vp-p (Inclusive)
Housing diameter	5/8 in, 3/8 in, 1/4 in, 10/32 in; various lengths	3/4 in, 5/8 in; various lengths	5/8 in, 3/8 in; various lengths
Housing material/style	Stainless steel/threaded or smooth	Stainless steel/ threaded	Stainless steel threaded or smooth
Termination	MS3106 connector, prelead	MS3106 connector, prelead	MS3106 connector, prelead
Operating temperature range	-55°C to 120°C [-67°F to 250°F] (Inclusive)	-73°C to 120°C [-100°F to 250°F] (Inclusive)	-55°C to 150°C [-67°F to 300°F] (Inclusive)



	VRS HIGH RESOLUTION	VRS HIGH TEMPERATURE	VRS POWER OUTPUT
Description/potential applications	Used where precise timing pulse is required, and/or fine pitch gears are used	Used where the sensor is exposed to temperatures up to 260°C [450°F] (sealed front-end versions for use where the sensor is exposed to fluids, lubricants or adverse environmental conditions)	Used where driving low resistance loads at large air gaps is required, and larger actuators are used
Output voltage range	8 Vp-p to 190 Vp-p (Inclusive)	4.7 Vp-p to 125 Vp-p (Inclusive)	70 Vp-p (Inclusive)
Housing diameter	5/8 in, 3/8 in; various lengths	5/8 in, 3/8 in, 1/4 in; various lengths	5/8 in; various lengths
Housing material/style	Stainless steel/threaded or smooth	Stainless steel threaded	Stainless steel, threaded
Termination	MS3106 connector, prelead	MS3106 connector, prelead	MS3106 connector, prelead
Operating temperature range	-55°C to 150°C [-67°F to 300°F] (Inclusive)	-73°C to 230°C [-100°F to 450°F] (Inclusive)	-55°C to 120°C [-67°F to 250°F]

For more information

Honeywell Sensing & Safety Technologies services its customers through a worldwide network of sales offices and distributors. For application assistance, current specifications, pricing or the nearest Authorized Distributor, visit [our website](#) or call:

USA/Canada	+1 302 613 4491
Latin America	+1 305 805 8188
Europe	+44 1344 238258
Japan	+81 (0) 3-6730-7152
Singapore	+65 6355 2828
Greater China	+86 4006396841

Honeywell Sensing & Safety Technologies

830 East Arapaho Road
Richardson, TX 75081
www.honeywell.com

WARRANTY/REMEDY

Honeywell warrants goods of its manufacture as being free of defective materials and faulty workmanship during the applicable warranty period. Honeywell's standard product warranty applies unless agreed to otherwise by Honeywell in writing; please refer to your order acknowledgement or consult your local sales office for specific warranty details. If warranted goods are returned to Honeywell during the period of coverage, Honeywell will repair or replace, at its option, without charge those items that Honeywell, in its sole discretion, finds defective. **The foregoing is buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Honeywell be liable for consequential, special, or indirect damages.**

While Honeywell may provide application assistance personally, through our literature and the Honeywell web site, it is buyer's sole responsibility to determine the suitability of the product in the application.

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this writing. However, Honeywell assumes no responsibility for its use.