

3GAA092520-ASJ



General Information

Product ID:	3GAA092520-ASJ
ABB Type Designation:	M3AA 90LB 4
Catalog Description:	No Description Available

Additional Information

ABB Type Designation:	M3AA 90LB 4
Bearing:	6205-2Z/C3
Bearing NDE:	6204-2Z/C3
Country of Origin:	Poland (PL) Finland (FI) Romania (RO)
Customs Tariff Number:	85015220
Direction of Rotation:	Both sides

Electrical Data:

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.10 kW	1437 r/min	2.46 A	0.780	84.10 %	7.32 N·m	6.90
D	--	50 Hz	230 V	1.10 kW	1437 r/min	4.27 A	0.780	84.10 %	7.32 N·m	6.90
Y	--	50 Hz	415 V	1.10 kW	1442 r/min	2.42 A	0.750	84.10 %	7.32 N·m	8.40

Gross Weight:	20 kg
IC Class:	IC411
IE Class Data (50 Hz):	IE Class IE3 Full Load (100%) 84.1 % Partial Load (75%) 83.6 % Partial Load (50%) 81.0 %
IM Class:	IMB3 IM1001
IP Class:	IP55
Insulation Class:	ICLF
Made To Order:	No
Minimum Order Quantity:	1 piece
Order Multiple:	1 piece
Package Level 1 Units:	0 carton
Poles (High):	4
Product Name:	3-Phase squirrel cage motor
Product Net Weight:	17 kg
Quote Only:	No
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Nordic Central Stock Spain CSI
Temperature Class Default:	--
Terminator Box Location:	D-End top
Two Speed Motor:	No
Voltage Code:	S