

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/gb/products/0830980>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: latching, Number of individual labels: 21, text field height: 17.4 mm, text field width: 27.9 mm

Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements
- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Commercial data

Item number	0830980
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2419
Product key	BG2419
Catalog page	Page 317 (C-3-2019)
GTIN	4046356913515
Weight per piece (including packing)	15.47 g
Weight per piece (excluding packing)	9.99 g
Customs tariff number	39269097
Country of origin	DE

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/gb/products/0830980>

Technical data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	21
Number of individual labels per row	3
Identification technology	Thermal transfer for sheets and cards

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	10 °C ... 25 °C
Recommended humidity (storage/transport)	35 % ... 65 %

Dimensions

Width	27.9 mm
Depth	0.5 mm
Length	17.4 mm
Material strength	0.50 mm

Text field

Text field width	27.9 mm
Text field height	17.4 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/gb/products/0830980>

Classifications

ECLASS

ECLASS-13.0	27281106
-------------	----------

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/gb/products/0830980>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.055 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk