

PRODUCT-DETAILS

TY800-120

CABLE TIE 120LB 28IN NATURAL NYLON



General Information

Extended Product Type	TY800-120
Product ID	7TAG054360R0347
EAN	5414363066774
Catalog Description	CABLE TIE 120LB 28IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 756mm (29.76 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.8mm (0.07 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds), Bulk Pack

Ordering

E-Number (Finland)	1381507
EAN	5414363066774
UPC	786210572864

Dimensions

Product Net Width	0.3 in 7.62 mm
Product Net Depth / Length	29.76 in 756 mm

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	2.5 in 64 mm
Package Level 1 Height	14 in 356 mm
Package Level 1 Depth / Length	38 in 965 mm
Package Level 2 Units	500 piece
Package Level 2 Width	8 in 203 mm
Package Level 2 Height	8.5 in 216 mm
Package Level 2 Depth / Length	38.5 in 978 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	8 in 203.2 mm
Color	Natural
Effective Date	19960529
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	120 lb 540 N
Thickness	0.07 in 1.8 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY800-120
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY800-120

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

