

## CONSTANT LEVEL TROLLEYS



50 - 100 KG

The FIMM trolley is equipped with a movable bottom allowing to work at an ergonomic height.

- Pantograph system with spring. Weight sensitivity of 300 g.
- PVC cladding made of expanded plastic, lightweight and easy to maintain.
- The welded steel frame is reinforced from underneath and guarantees a very good resistance in time. CU of the frame: 500 kg.
- Backrest made of Ø 28 mm tube for a good grip. Ergonomic pushing height 1020 mm. Useful height of the backrest: 500 mm.
- Melamine top, thickness 16 mm.
- 2 fixed + 2 swivel wheels with brakes, mounted on ball bearings, non-marking and silent. 50% less starting effort. Complies with the EN 1757 standard.
- Delivered assembled.



Reference	CU	Tray travel	Overall dimensions mm	Ø Wheels	Bandage	Weight
800 004 058	50	400	1200 x 700 x 1020	200	TPE	68
800 004 059	100		1400 x 800 x 1020			74

## PRODUCT ZOOM



Constant level by pantograph system with spring.



## OPTIONS

Customisation option for back and side panels

802 000 026 - Personalization by printing 1 folder

802 000 027 - Personalization by printing 1 side panel

802 000 028 - Customised by printing on 2 folders + 2 sides



## OTHER MODELS AVAILABLE



CU 20 to 200 kg



CU 25 to 100 kg