

Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

KONTAKT PCC
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Smedsgatan 3-5 LT4, PL62, 08101 LOJO	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008**

Physical:

Aerosols, category 1

**CRC Industries Europe bvba**Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

1 / 12

Productname :	KONTAKT PCC	Creationdate :	04.03.19 Version : 1.0
Ref.Nr.:	BDS002425_3_20190304 (EN)	Replaces:	

Extremely flammable aerosol.
Pressurised container: May burst if heated.

Classification is based on test data.

Health: Eye irritation, category 2
Causes serious eye irritation.
Specific target organ toxicity - single exposure, category 3
May cause drowsiness or dizziness.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 3
Harmful to aquatic life with long lasting effects.


Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
propan-2-ol; isopropyl alcohol ;isopropanol

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.
H229 : Pressurised container: May burst if heated.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.
H412 : Harmful to aquatic life with long lasting effects.

Precautionary statement(s): P102 : Keep out of reach of children.
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 : Do not spray on an open flame or other ignition source.
P251 : Do not pierce or burn, even after use.
P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
P271 : Use only outdoors or in a well-ventilated area.
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501-2 : Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information: Repeated exposure may cause skin dryness or cracking.

Regulation (EC) No 648/2004 on detergents: aliphatic hydrocarbons 15 - 30 %

2.3. Other hazards

No information available

Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

SECTION 3: Composition/information on ingredients**3.1. Substances**

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	25-50	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
ethanol; ethyl alcohol	01-2119457610-43	64-17-5	200-578-6	10-25	Flam. Liq. 2, Eye Irrit. 2	H225,H319	B,X,W
Hydrocarbons, C6-C7, isoalkanes, cyclics, < 5% n-hexane	01-2119486291-36	-	(926-605-8)	10-25	Flam. Liq. 2, Asp. Tox. 1, STOT SE 3, Aquatic Chronic 2	H225,H304,H336,H411	B,Q
methylal	01-2119664781-31	109-87-5	203-714-2	5-10	Flam. Liq. 2	H225	B
carbon dioxide	-	124-38-9	204-696-9	5-10	Press. Gas	H280	A,G
1-ethoxypropan-2-ol	01-2119462792-32	1569-02-4	216-374-5	5-10	Flam. Liq. 3, Eye Irrit. 2, STOT SE 3	H226,H319,H336	
methanol	01-2119433307-44	67-56-1	200-659-6	<1	Flam. Liq. 2, Acute Tox. 3, Acute Tox. 3, Acute Tox. 3, STOT SE 1	H225,H331,H311,H301,H370	A,X
butanone; ethyl methyl ketone	01-2119457290-43	78-93-3	201-159-0	<1	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	A

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

W : Note: substance mentioned on the list of CMR-substances of the Dutch Ministry of Social Affairs and Employment (SZW)

X : SCL (specific concentration limit)in accordance with art.10 of CLP Regulation No 1272/2008

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures**4.1. Description of first aid measures****Contact with eyes :**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
If eye irritation persists: Get medical advice/attention.

Contact with skin :

Take off contaminated clothing and wash before reuse.
IF ON SKIN: Wash with plenty of soap and water.
If skin irritation occurs: Get medical advice/attention.



Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

Inhalation : IF INHALED: Remove person to fresh air and keep comfortable for breathing.
Call a POISON CENTER or doctor/physician if you feel unwell.

Ingestion : If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation : Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness

Ingestion : May cause gastrointestinal disturbances
Symptoms : sore throat, abdominal pain, nausea, vomiting

Skin contact : May cause irritation.
Symptoms : redness and pain

Eye contact : Irritating to eyes
Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO₂

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.



Productname : KONTAKT PCC**Creationdate :**04.03.19 Version :
1.0**Ref.Nr.:** BDS002425_3_20190304 (EN)**Replaces:**

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.
Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Precision

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :



Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
carbon dioxide	124-38-9	TWA	9000 mg/m3
		STEL	mg/m3
methanol	67-56-1	TWA	200 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm
National established exposure limits, United Kingdom			
methylal	109-87-5	TWA	1000 ppm
		STEL	1250 ppm
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
ethanol; ethyl alcohol	64-17-5	TWA	1000 ppm
methanol	67-56-1	TWA	200 ppm
		STEL	250 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm
National established exposure limits, Ireland			
methylal	109-87-5	TWA	1000 ppm
		STEL	-
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
ethanol; ethyl alcohol	64-17-5	STEL	1000 ppm
methanol	67-56-1	TWA	200 ppm
		STEL	-
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	200 ppm
		STEL	400 ppm
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm

8.2. Exposure controls

Control procedures :

Ensure adequate ventilation
 Keep away from heat and sources of ignition
 Take precautionary measures against static discharges

Personal protection :

Take precautions to avoid contact with skin and eyes when handling the product.
 Ensure adequate ventilation
 Wear suitable protective gloves

inhalation :

In case of insufficient ventilation, wear suitable respiratory equipment.

recommended respiratory protection:

Air purifying respirator equipped with organic gas/vapor cartridge (type AX)

hands and skin :

When handling the product wear chemical-resistant gloves (standard EN



Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

374).

The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.

Recommended gloves:

Nitrile

eyes :

Wear safety eyewear according to EN 166.

Environmental protection:

Avoid release to the environment.

Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state : CO2 propelled liquid.
colour : Colorless.
odour : Solvent.
pH : Not applicable.
Boiling point/range : 42-132 °C
Flash point : - 20 °C (Closed Cup)
Evaporation rate : Not available.
Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : Not available.
Relative density : 0.79 g/cm3 (@ 20°C).
Solubility in water : Insoluble in water
Auto-ignition : > 200 °C
Viscosity : 1.17 mPa.s (@ 20°C).

9.2. Other information

VOC = volatile organic compounds 750 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions



Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	Causes serious eye irritation.
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances
Skin contact :	May cause irritation.
Eye contact :	Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
methylal	109-87-5	LD50 oral rat	6423 mg/kg
		LD50 derm.rabit	> 5000 mg/kg
1-ethoxypropan-2-ol	1569-02-4	LD50 oral rat	> 2000 mg/kg
		LC50 inhal.rat	> 9.59 mg/l



Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

		LD50 derm.rabit	> 2000 mg/kg
ethanol; ethyl alcohol	64-17-5	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	5840 mg/kg
		LC50 inhal.rat	> 25000 mg/l
		LD50 derm.rabit	13900 mg/kg
butanone; ethyl methyl ketone	78-93-3	LD50 oral rat	> 2000 mg/kg
Hydrocarbons, C6-C7, isoalkanes, cyclics, < 5% n-hexane	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 3
Harmful to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
methylal	109-87-5	LC50 fish	> 1000 mg/l
		EC50 daphnia	> 1000 mg/l
1-ethoxypropan-2-ol	1569-02-4	IC50 algae	> 100 mg/l
		LC50 fish	6812 mg/l
		EC50 daphnia	1929 mg/l
ethanol; ethyl alcohol	64-17-5	LC50 fish	> 100 mg/l
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	1000 mg/l
		LC50 fish	9640 mg/l
		EC50 daphnia	9714 mg/l
Hydrocarbons, C6-C7, isoalkanes, cyclics, < 5% n-hexane	-	IC50 algae	55 mg/l
		LC50 fish	12 mg/l
		EC50 daphnia	3 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil



Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effectsNo experimental data available
GWP (global warming potential): 0**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information**14.1. UN number**

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)Class: 2.1
ADR/RID - Classification code: 5F**14.4. Packing group**

Packing group: Not applicable.

14.5. Environmental hazardsADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No**14.6. Special precautions for user**

Productname : KONTAKT PCC

Creationdate :

04.03.19 Version :

Ref.Nr.: BDS002425_3_20190304 (EN)

Replaces:

1.0

ADR/RID - Tunnelcode:	(D)
IMDG - Ems:	F-D, S-U
IATA/ICAO - PAX:	203
IATA/ICAO - CAO	203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008 (CLP)
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H301 : Toxic if swallowed.
H304 : May be fatal if swallowed and enters airways.
H311 : Toxic in contact with skin.
H319 : Causes serious eye irritation.
H331 : Toxic if inhaled.
H336 : May cause drowsiness or dizziness.
H370 : Causes damage to organs .
H411 : Toxic to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistent bioaccumulative toxic
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental



Productname : KONTAKT PCC**Creationdate :**04.03.19 Version :
1.0**Ref.Nr.:** BDS002425_3_20190304 (EN)**Replaces:**

risks, no part of these documents may be reproduced by any process without written permission from CRC.

