

Price\* : 119.16 GBP



### Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

### Complementary

Colour	Black
Material	PC (polycarbonate) (terminal cover) ABS (acrylonitrile butadiene-styrene) (body)
Product weight	0.18 kg
Marking	CE
Overvoltage category	Class II conforming to EN/IEC 61140
Mounting support	72 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	117 mA at 12 V 125 mA at 24 V 158 mA at 12 V 200 mA at 24 V
Clamping connection capacity	$\leq 1 \times 1.5 \text{ mm}^2$
Width	72 mm
Height	72 mm
Depth	69.3 mm

### Environment

Discrete output type	NPN
Signalling type	16 tones alarm
Standards	EN/IEC 61000-6-2 EN/IEC 61000-6-3 UL 464
Product certifications	UR
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C

IP degree of protection	IP54 (panel mounted) conforming to EN/IEC 60529
Noise level	0...90 dB (continuous or intermittent tone) at 1 m

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1346 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Electronic Alarm

Dimensions

