

Technical data

4T-3578/3525

Single row tapered roller bearings



Tapered roller bearing, pressed steel cage

KIT CONTENT

4T-3525, 4T-3578

VISUAL (S)



4T-3578/3525
Single row tapered roller bearings



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	44,45 mm
D - External diameter	87,312 mm
B - Bearing/Inner ring width	30,886 mm
C - Outer ring width	23,812 mm
T - Total width	30,162 mm
d1 - External diameter inner ring	63,6 mm
a - Charge load application point	20,162 mm
Mass	0,78 kg

PRODUCT PERFORMANCE	
C - Dynamic load	104 kN
C0 - Static load	117 kN
Cu - Fatigue limit load	14,3 kN

PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.31
Y0 - Static axial load coefficient	1.08
Y2 - Upper axial load coefficient	1.96
N lim - Oil lubrication limit speed	5900 tr/min
N lim - Grease lubrication limit speed	4400 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	51 mm
db min - Min IR shoulder diameter	57 mm
Da max - Max shoulder diameter OR	75 mm
Db min - Min OR shoulder diameter	81 mm
ra max - Max fillet radius	3,5 mm
r1a - Max fillet radius	3,3 mm

KIT COMPONENT

Cone designation	4T-3578
Cup designation	4T-3525

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-3578/3525
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material

Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

Fa / Fr ≤ e		Fa / Fr > e	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X _o	Y _o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table

