


SuperSOT
SOT23 NPN SILICON POWER
(SWITCHING) TRANSISTORS
ISSUE 3 - NOVEMBER 1995

FMMT617 FMMT618
FMMT619 FMMT624
FMMT625

FEATURES

- * **625mW POWER DISSIPATION**
- * I_C CONT 3A
- * 12A Peak Pulse Current
- * Excellent H_{FE} Characteristics Up To 12A (pulsed)
- * Extremely Low Saturation Voltage E.g. 8mV Typ.
- * Extremely Low Equivalent On Resistance; $R_{CE(sat)}$



DEVICE TYPE	COMPLEMENT	PARTMARKING	$R_{CE(sat)}$
FMMT617	FMMT717	617	50mΩ at 3A
FMMT618	FMMT718	618	50mΩ at 2A
FMMT619	FMMT720	619	75mΩ at 2A
FMMT624	FMMT723	624	-
FMMT625	-	625	-

ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	FMMT 617	FMMT 618	FMMT 619	FMMT 624	FMMT 625	UNIT
Collector-Base Voltage	V_{CBO}	15	20	50	125	150	V
Collector-Emitter Voltage	V_{CEO}	15	20	50	125	150	V
Emitter-Base Voltage	V_{EBO}	5	5	5	5	5	V
Peak Pulse Current**	I_{CM}	12	6	6	3	3	A
Continuous Collector Current	I_C	3	2.5	2	1	1	A
Base Current	I_B			500			mA
Power Dissipation at $T_{amb}=25^\circ\text{C}^*$	P_{tot}			625			mW
Operating and Storage Temperature Range	T_j, T_{stg}			-55 to +150			°C

* Maximum power dissipation is calculated assuming that the device is mounted on a ceramic substrate measuring 15x15x0.6mm

**Measured under pulsed conditions. Pulse width=300μs. Duty cycle ≤ 2%
Spice parameter data is available upon request for these devices


FMMT617

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^\circ C$ unless otherwise stated).

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	15	70		V	$I_C=100\mu A$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	15	18		V	$I_C=10mA^*$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	5	8.2		V	$I_E=100\mu A$
Collector Cut-Off Current	I_{CBO}			100	nA	$V_{CB}=10V$
Emitter Cut-Off Current	I_{EBO}			100	nA	$V_{EB}=4V$
Collector Emitter Cut-Off Current	I_{CES}			100	nA	$V_{CES}=10V$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		8 70 150	14 100 200	mV mV mV	$I_C=0.1A, I_B=10mA^*$ $I_C=1A, I_B=10mA^*$ $I_C=3A, I_B=50mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$		0.9	1.0	V	$I_C=3A, I_B=50mA^*$
Base-Emitter Turn-On Voltage	$V_{BE(on)}$		0.84	1.0	V	$I_C=3A, V_{CE}=2V^*$
Static Forward Current Transfer Ratio	h_{FE}	200 300 200 150	415 450 320 240 80			$I_C=10mA, V_{CE}=2V^*$ $I_C=200mA, V_{CE}=2V^*$ $I_C=3A, V_{CE}=2V^*$ $I_C=5A, V_{CE}=2V^*$ $I_C=12A, V_{CE}=2V^*$
Transition Frequency	f_T	80	120		MHz	$I_C=50mA, V_{CE}=10V$ $f=50MHz$
Output Capacitance	C_{obo}		30	40	pF	$V_{CB}=10V, f=1MHz$
Turn-On Time	$t_{(on)}$		120		ns	$V_{CC}=10V, I_C=3A$ $I_{B1}=I_{B2}=50mA$
Turn-Off Time	$t_{(off)}$		160		ns	


*Measured under pulsed conditions. Pulse width=300μs. Duty cycle ≤ 2%

TYPICAL CHARACTERISTICS




FMMT619

TYPICAL CHARACTERISTICS




I_C - Collector Current (A)

$V_{CE(\text{SAT})}$ vs I_C




Collector Current

$V_{CE(\text{SAT})}$ vs I_C




Collector Current

HFE vs I_C




Collector Current

$V_{BE(\text{SAT})}$ vs I_C




Collector Current

$V_{BE(\text{ON})}$ vs I_C




PACKAGE OUTLINE DETAILS

SOT223




DIM	Millimeters		Inches	
	Min	Max	Min	Max
A	6.3	6.7	0.248	0.264
B	3.3	3.7	0.130	0.146
C	-	1.7	-	0.067
D	0.6	0.8	0.024	0.031
E	2.9	3.1	0.114	0.122
F	0.24	0.32	0.009	0.013
G	NOM 4.6		NOM 0.181	
H	0.85	1.05	0.033	0.041
K	0.02	0.10	0.0008	0.004
L	6.7	7.3	0.264	0.287
M	NOM 2.3		NOM 0.0905	

SOT89



DIM	Millimeters		Inches	
	Min	Max	Min	Max
A	4.40	4.60	0.173	0.181
B	3.75	4.25	0.150	0.167
C	1.40	1.60	0.0550	0.0630
D	-	2.60	-	0.102
F	0.28	0.45	0.011	0.018
G	0.38	0.55	0.015	0.022
H	1.50	1.80	0.060	0.072
K	2.60	2.85	0.102	0.112
L	2.90	3.10	0.114	0.122
N	1.40	1.60	0.055	0.063

SOT23



DIM	Millimeters		Inches	
	Min	Max	Min	Max
A	2.67	3.05	0.105	0.120
B	1.20	1.40	0.047	0.055
C	-	1.10	-	0.043
D	0.37	0.53	0.0145	0.021
F	0.085	0.15	0.0033	0.0059
G	NOM 1.9		NOM 0.075	
K	0.01	0.10	0.0004	0.004
L	2.10	2.50	0.0825	0.0985
N	NOM 0.95		NOM 0.37	

THERMAL RESISTANCE AND DERATING INFORMATION


D) SOT23 625 mW devices

$\theta_{j-c}=100^\circ\text{C}/\text{W}$ Typical

$\theta_{j-a}=190^\circ\text{C}/\text{W}$ Typical

= $200^\circ\text{C}/\text{W}$ Maximum

Mounted on a 15 x 15 x 0.6 mm alumina substrate connected using 25mm x 0.5mm dia copper wire





E) SOT23 500 mW devices

$\theta_{j-c}=110^\circ\text{C}/\text{W}$ Typical

$\theta_{j-a}=200^\circ\text{C}/\text{W}$ Typical

= $250^\circ\text{C}/\text{W}$ Maximum

Mounted on a 15 x 15 x 0.6 mm alumina substrate connected using 25mm x 0.5mm dia copper wire



*330mW shown for reference only