


**FAG****6317-C4**

Deep groove ball bearing

Deep groove ball bearing 63, single row, steel
sheet metal cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	85 mm	Bore diameter
D	180 mm	Outside diameter
B	41 mm	Width
C_r	141,000 N	Basic dynamic load rating, radial
C_{0r}	97,000 N	Basic static load rating, radial
C_{ur}	6,000 N	Fatigue load limit, radial
n_G	5,000 1/min	Limiting speed
n_{gr}	5,300 1/min	Reference speed
$\approx m$	4.25 kg	Weight



Mounting dimensions

d _{a min}	99 mm	Minimum diameter shaft shoulder
D _{a max}	166 mm	Maximum diameter of housing shoulder
r _{a max}	2.5 mm	Maximum fillet radius

Dimensions

r _{min}	3 mm	Minimum chamfer dimension
D ₁	151.58 mm	Shoulder diameter outer ring
d ₁	114.36 mm	Shoulder diameter inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	150 °C	Operating temperature max.

Calculation factors

f ₀	13.3	Calculation factor
----------------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed