

SACC-CIP-M12MS-17P SMD SH R32X - Contact carrier



1238961

<https://www.phoenixcontact.com/gb/products/1238961>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 17-position, Pin, straight, M12, A-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

Item number	1238961
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABQBGB
Product key	ABQBGB
GTIN	4063151459031
Weight per piece (including packing)	6.77 g
Weight per piece (excluding packing)	3.956 g
Country of origin	DE

SACC-CIP-M12MS-17P SMD SH R32X - Contact carrier



1238961

<https://www.phoenixcontact.com/gb/products/1238961>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Signal
Number of positions	17
No. of control contacts	17
Seal present	yes
Shielded	yes
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	1.5 A

Connection data

Connection method	SMD reflow
-------------------	------------

Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

Connector

Connection 1

Head design	Pin
Head cable outlet	straight

SACC-CIP-M12MS-17P SMD SH R32X - Contact carrier



1238961

<https://www.phoenixcontact.com/gb/products/1238961>

Head thread type	M12
Coding	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 105 °C
	-55 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad

SACC-CIP-M12MS-17P SMD SH R32X - Contact carrier




1238961

<https://www.phoenixcontact.com/gb/products/1238961>

Drawings

Schematic diagram



Pin assignment M12 male connector, 17-pos., male side view

SACC-CIP-M12MS-17P SMD SH R32X - Contact carrier



1238961

<https://www.phoenixcontact.com/gb/products/1238961>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1238961>

 cULus Recognized Approval ID: E221474-20160506				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1.5 A	-	-

SACC-CIP-M12MS-17P SMD SH R32X - Contact carrier



1238961

<https://www.phoenixcontact.com/gb/products/1238961>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SACC-CIP-M12MS-17P SMD SH R32X - Contact carrier



1238961

<https://www.phoenixcontact.com/gb/products/1238961>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk