

Kaedra - for modular device - 2 x 12 modules - 1+1 terminal blocks

Local distributor code: 391535886

13983

EAN Code: 3303430139836

Main

Range	Mureva	
product name	Mureva Enclosure	
Product or component type	Weatherproof enclosure	
Enclosure type	Enclosure for modular device	
Mounting plate description	Slotted	

Complementary

Enclosure mounting	Surface	
9 mm pitches	24	
Number of 18 mm modules per row	12	
Total number of 18 mm modules	24	
Number of horizontal rows	2	
Electrical insulation class	Double insulation Class II	
Provided equipment	2 marking kit 2 wiring strap 1 terminal block 32 holes 1 terminal block support	
Type of front cover	Transparent Reversible	
Power dissipation in W	34 W	
[In] rated current	63 A	
Type of rail	DIN	
Number of pre-cutouts PG ISO	17	
Number of terminal blocks	1 earth (screw connection) with 32 outgoers	
Distribution block outgoers	16 x 16 mm² + 16 x 10 mm²	
Locking options description	Optional keylock	
Enclosure material	Self-extinguishing polymer	
Width	340 mm	
Height	460 mm	
Depth	160 mm	
Internal depth	88 mm	
Colour	Door: transparent green Enclosure: light grey (RAL 7035)	

Environment

Standards	IEC 61439-3 EN 50262 IEC 60695-2-1 IEC 60670	
Fire resistance	650 °C conforming to IEC 60695-2-1	
IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK09 conforming to EN 50102	
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013	
Overvoltage category	II	
Ambient air temperature for operation	-2560 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.000 cm
Package 1 Width	36.000 cm
Package 1 Length	47.500 cm
Package 1 Weight	3.433 kg
Unit Type of Package 2	P12
Number of Units in Package 2	28
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	108.000 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months

1 Jul 2025



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	19
Environmental Disclosure	Product Environmental Profile

Use Better

Minimum percentage of recycled plastic content	27
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	5305d5d6-3783-4b3d-abd0-61fa4a6023d7
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free product

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Exploded view

