

Plunge Cut Saw LXT®

DSP600

18V X2 • 2 500 – 6 300 min⁻¹ • 165 mm

Precise brushless plunge cut circular saw for professional use

A precise plunge cut circular saw with a brushless motor. Two 18V LXT® batteries offer a voltage of 36V. This fast saw has an adjustable speed of between 2 500 and 6 300 min⁻¹. Achieves neat cutting results when used with a guide rail.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Max. Cutting Depth at 90°	56 mm
Max. Cutting Depth at 45°	40 mm
No load speed	2500 - 6300 min ⁻¹
Sound Power Level (L _{WA})	103 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	4,4 - 5,1 kg
Product Dimensions (L x W x H):	346 x 241 x 272 mm
Brushless Motor	✓
Max. Cutting Depth at 48°	38 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Bevel Range (Right)	-1 - 48 °

User benefits

- Brushless maintenance-free and long-life motor
- Soft start for smooth start-ups
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Electric brake for maximum productivity and increased operator safety
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

165447-6

Parallel Guide



194367-7

Guide rail, 3 000 mm



196664-7

Bevel guide set



198885-7

Guide rail joint connector set, 2 pcs



199140-0

Guide rail, 1 000 mm



199826-6

Quick-Release Ratcheting Guide Rail



821552-6

Makpac case (4)



839290-6

MakPac (4) Inlay



Other

User manual

Parts drawing