




Connectors > Rectangular Connectors > Standard Rectangular Connectors > AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Connector Assembly**

Mating Retention Type: **Lock**

Connector System: **Wire-to-Board**

Number of Positions: **11**

Centerline (Pitch): **2 mm [.079 in]**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	11
Number of Rows	1

Contact Features

Contact Current Rating (Max)	3 A
------------------------------	-----

Mechanical Attachment

Mating Retention Type	Lock
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2 mm[.079 in]

Usage Conditions

--	--



Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-292254-1
CT RELAY HDR ASSY 11P NAT




TE Part # CAT-3980408-PHDWKV
CT 2mm Post Header Assembly with Kink - Vertical




TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME




TE Part # 6-292271-1
MT REC ASSY AU-PL. 11P BLUE




TE Part # 1-292133-1
CT P/HDR ASSY BOX V 11P W/O KI




TE Part # 1-292164-1
CT P/HDR BOX H ASSY 11P T/P NA



TE Part # 1-292250-1
CT P/HDR BOX H ASSY 11P W/KINK




TE Part # 1-292165-1
CT P/HDR BOX V 11P T/P NAT



TE Part # 1-292166-1
CT P/HDR BOX V 11P T/P NAT W/O



TE Part # 1-292271-1
MT REC ASSY AU-PL. 11P GRAY




TE Part # CAT-3983178-PHBXVD
CT 2mm Post Header Asmbly: Box V DIP




TE Part # 1-292207-1
MINI CT SGL DIP V 11P NAT DIP



TE Part # 58372-1
HEAD (IDC) 2MM C.T. W/O TL



TE Part # CAT-3980407-RHDRRA
CT 2mm Header Assembly: Right Angle



TE Part # 1-292215-1
MINI CT SGL RELAY 11P NAT


Also in the Series | AMP CT



Connector Contacts(8)



Connector Hardware(46)



PCB Headers & Receptacles(756)




Rectangular Connector Housings(72)




Rectangular Power Connectors(906)



Standard Rectangular Connectors(158)




Wire-to-Board Connector Assemblies & Housings(97)



Wire-to-Board Headers & Receptacles (756)

Customers Also Bought



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-179694-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-179694-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-179694-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

Product Specifications

Application Specification

English