



tesa® Powerstrips Waterproof Strips Large



Product Information

BNR 59700, 59774

Product Description

tesa Powerstrips Waterproof are large self-adhesive mounting strips made for the removable wall fixation of objects weighing up to 2 kg. tesa Powerstrips Waterproof are large self-adhesive mounting strips made for the removable wall fixation of objects weighing up to 2 kg.

Product Features

- Especially developed to fix objects in wet areas (e.g. shower, bathtub, etc.)
- Maximum hold of up to 2 kg on smooth surfaces
- Removable without a trace due to the Powerstrips® Waterproof technology
- Maximum hold of up to 2 kg on smooth surfaces
- Strong hold for objects on surfaces like tiles, glass, etc.*
- Suitable for the whole Powerstrips Waterproof accessory range

*Not suitable for use on styrofoam, foamed material, surfaces with non-stick coating, porous material

- Especially developed to fix objects in wet areas (e.g. shower, bathtub, etc.)
- Maximum hold of up to 2 kg on smooth surfaces
- Removable without a trace due to the Powerstrips® Waterproof technology
- Maximum hold of up to 2 kg on smooth surfaces
- Strong hold for objects on surfaces like tiles, glass, etc.*
- Suitable for the whole Powerstrips Waterproof accessory range

*Not suitable for use on styrofoam, foamed material, surfaces with non-stick coating, porous material

Application Fields

How to apply - step by step guide: 1. Clean the surface with alcohol or silicone-free glass cleaner

2. Take the included waterproof primer tissue and wipe over the surface for bonding preparation - wait for 10 seconds minimum

3. Apply the Powerstrip Waterproof Large strip on the object - press for 5 seconds minimum

4. Fix object onto surface - press for 5 seconds minimum

5. Make sure the tab can be accessed for removal

How to apply - step by step guide: 1. Clean the surface with alcohol or silicone-free glass cleaner

2. Take the included waterproof primer tissue and wipe over the surface for bonding preparation - wait for 10 seconds minimum

3. Apply the Powerstrip Waterproof Large strip on the object - press for 5 seconds minimum

4. Fix object onto surface - press for 5 seconds minimum

5. Make sure the tab can be accessed for removal



tesa® Powerstrips Waterproof Strips

Large

Product Information

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Type of adhesive	synthetic rubber	• Holding power up to	2 Kg
• Total thickness	650 µm	• Hook shape	_NULL
• Holding power of strip up to	2 Kg		

Properties/Performance Values

• Ageing resistance (UV)	yes	• Ozone resistance	yes
• Application temperature	from 20°C up to 25°C	• Residue free removal	yes
• Application temperature from	-15 °C	• Reusable	no
• Applicationfield	Bathroom, Kitchen	• Reusable with	_NULL
• Area of use	Indoor	• Solvent free	no
• Batteries included	no	• Suitable surfaces	Even wood, Tiles, Most plastics, Glass, Acrylic glass, Steel, Metal
• Batteries required	no		
• Chemical resistance	no		
• Hazard material	yes		
• Humidity resistance	yes	• Temperature resistance max.	35 °C
• Material	_NULL	• Temperature resistance min.	5 °C
• Oil and grease resistance	no	• UV-resistant	no
		• Water resistance	yes
		• Waterproof	yes

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?cp=NaN>