



DELTA SCHUKO DOUBLE SOCKET OUTL 10/16A
250V, TITANIUM WHITE W. SCREW TERMINALS F.
SWITCH BOXES D=58MM COVER PLATE 117X80MM

Model		
Design of the product		SCHUKO
Cover version		solid plate
Design of the special power supply unit		without special current supply
Design of the socket / according to VDE 0620 for severe conditions		No
Design of the phase tap		Without
General technical data		
Marking / of socket outlet		without imprint
Mounting type		fixing with claw and screw
Surface processing		others
Material		thermoplastic
Protection class		
Protection class IP		IP20
Main circuit		
Operating frequency		
• minimum	Hz	50
• maximum	Hz	50
Operating voltage / Rated value	V	250
Operating current / Rated value	A	16
Appearance		
Color		white
Product details		

Product component		
• Ejection equipment		No
• Labeling field		No
• Increased touch protection		No
• Fault current protection		No
• miniature fuse		No
• Integrated / functional lighting		No
• Integrated / Light source		No
• Integrated / orientation lighting		No
• Hinged lid		No
Product property		
• lockable		No
• halogen-free		Yes
• transparent		No

Product function

Product function		
• Socket selectable		No
• Overvoltage protection		No

Number

Number of units		2
Number of sockets / switchable		0

Connections

Arrangement of contacts / diagonal		No
Type of electrical connection		plug terminal

Mechanical Design

Height	mm	117
Width	mm	80
Depth	mm	60
Mounting type		flush mounted
Material / of the enclosure		plastic

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5UB2201>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5UB2201/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5UB2201

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

05.05.2015