



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	.7 – 10.2 kgf

Dimensions

Product Length	21.2 mm[.834 in]
Compatible Insulation Diameter Range	2.21 – 3.4 mm[.087 – .134 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 234619-1 DAHT P L EX & EX II 18-14 ASSY	 TE Part # 175022-2 250 POSITIVE REC EX MK-2	 TE Part # 2376595-2 250 FASTON PCB TAB TPBR	 TE Part # 2376579-2 250 FASTON PCB TAB TPBR
 TE Part # 2232343-2 250 PL EX FLAG REC. 18-12AWG PTBR FLAT	 TE Part # 2232343-1 250 PL EX FLAG REC. 18-12AWG PTBR	 TE Part # 2376582-2 250 FASTON PCB TAB TPBR	 TE Part # 2376591-2 250 FASTON PCB TAB TPBR

Also in the Series | Positive Lock 250

 Automotive Terminals(1)	 Crimp Terminal Housings(177)	 Insertion & Extraction Tools(3)	 Insulation Boots & Sleeves(5)
--	--	--	--



Quick Disconnects(173)

Customers Also Bought

TE Part #1-2176331-4
CRGP 2512 120R 1%

TE Part #5-146256-5
10 MODII HDR DRST B/A .100CL L

TE Part #3-2176057-5
RLP73K 3A R27 1% 1K RL

TE Part #292304-5
STD USB TYPE B, R/A, T/H, 30U" AU

TE Part #170054-1
FF 250 REC 20-14AWG BR LP

TE Part #2-1418437-1
6POS,AMP MCP2.8,REC HSG,ASSY, SEALED

TE Part #8-328527-1
TERMINAL,PG R 16-14 8

TE Part #170148-1
MATE-N-LOK SOC LP

TE Part #2176248-4
TJT 250W 3R3 5%

TE Part #044579-E
ERMBUG L 6 1 172 E3 * J 2 44579 BUCHSENG

Documents

Product Drawings
PL 250 RECEPTACLE 18-14 AWG PTBR
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_175023-1_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_175023-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_175023-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[POSITIVE LOCK EX CONTACT](#)

English