



Afficher les détails du produit dans medias

10.11.2025, 03:05:57 UTC

SCHAFFLER




HEATER400-SMART-400V

Appareil de chauffage, inductif

HEATER smart

Information technique



Votre alternative produit actuelle

Series	SMART	Extended functionality

Données techniques

U	400 V	Tension de fonctionnement
f	50 – 60 Hz	Fréquence
P	12 kVA	Consommation électrique
I	30 A	Courant nominal
θ h max	240 °C	Max. heating temperature
	0 – 99 min	Heating time
	Touch	Display
	2	Magnetic probe, quantity
≈m	176 kg	Poids



Afficher les détails du produit dans medias

10.11.2025, 03:05:57 UTC

SCHAFFLER

Fonctions

+ + + + + + + + only in temp. and speed mode +	Temperature hold Automatic demagnetization, <2A/cm Swivel arm Log function Delta-T control Temperature control Time control Temperature and time control Temperature and speed control Overheating protection Automatic power reduction Device supports horizontal / lying heating of the workpiece Device supports vertical / hanging heating of the workpiece Device mobile
---	--

Dimensions

1.214 mm	Longueur du HEATER
560 mm	Largeur du HEATER
990 mm	Hauteur du HEATER
B 320 mm	Space between poles
C 305 mm	Pole length
D 80x100	Pole cross section (mm ²)



Afficher les détails du produit dans medias

10.11.2025, 03:05:57 UTC

SCHAFFLER

Pièce à chauffer

115 mm		Min. inner diameter workpiece, vertical heating: with included yoke
30 mm		Min. inner diameter workpiece, vertical heating: with optional yoke
135 mm		Min. inner diameter workpiece, horizontal heating
ØA max	850 mm	Diamètre extérieur max. de la pièce
315 mm		Max. workpiece width, vertical heating
300 mm		Max. workpiece width, horizontal heating
m b max	400 kg	Poids max. de la pièce

information additionnelle

1		Yokes included, quantity
80x80		Yokes included, cross section (mm ²)