

KVR800D2N5/1G

1GB 128M x 64-Bit DDR2-800

CL5 240-Pin DIMM

DESCRIPTION:

This document describes ValueRAM's 128M x 64-bit 1GB (1024MB) DDR2-800 CL5 SDRAM (Synchronous **DRAM**) memory module. The components on this module include eight 128M x 8-bit DDR2-800 SDRAM in FBGA packages. This 240-pin DIMM uses gold contact fingers and requires +1.8V. The electrical and mechanical specifications are as follows:

FEATURES:

✓ Clock Cycle Time (tCK) CL=5	2.5ns (min.) / 8ns (max.)
✓ Row Cycle Time (tRC)	57.5ns (min.)
✓ Refresh to Active/Refresh Command Time (tRFC)	127.5ns
✓ Row Active Time (tRAS)	45ns (min.) / 70,000ns (max.)
✓ Single Power Supply of	+1.8V (+/- .1V)
✓ Power	1.355 W (operating)
✓ UL Rating	94 V - 0

Note: The module defined in this data sheet is one of several configurations available under this part number. While all configurations are compatible, the DRAM combination and/or the module height may vary from what is described here.




Figure 1: KVR800D2N5/1G 240-Pin DIMM