

RAYCHEM

TE Internal #: 339267-000


T Shape Cable Transistion, 3 Branches , 25 Material Code, 25

Material Systems Code, -75 – 150 °C [-103 – 302 °F], 225 Adhesive Code

[View on TE.com >](#)



Wire Protection & Management > Heat Shrink Shapes > Cable Transitions & Breakouts



Molded Part Shape: **T Shape**

Number of Branches & Legs: **3**

Material Code: **25**

Material Systems Code: **25**

Adhesive Requirement: **Adhesive Precoat**

Features

Product Type Features

Molded Part Shape	T Shape
-------------------	---------

Configuration Features

Number of Branches & Legs	3
Adhesive Requirement	Adhesive Precoat

Body Features

Primary Product Material	Fluid Resistant Modified Elastomer
Material Code	25
Material Systems Code	25

Dimensions

Inside Diameter Range (Leg 2)	3.8 – 6.6 mm[.15 – .26 in]
Inside Diameter Range (Leg 1)	3.8 – 6.6 mm[.15 – .26 in]
Inside Diameter Range (Body)	7.4 – 13.2 mm[.29 – .52 in]

Usage Conditions

Operating Temperature Range	-75 – 150 °C[-103 – 302 °F]
Resistance Protection	Long-Term Fluid Exposure at High Temperatures

Other

Molded Part Shape Code	322A
------------------------	------



Size Code	012
Adhesive Code	225

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9-120035-5
[HarnWare/HarnVis Purchase Charge](#)



TE Part # 9-120035-6
[HarnWare/HarnVis Renewal Charge](#)

Customers Also Bought



TE Part #1-1616992-7
K500A1C=CONTACTOR SPST NO DB
500 AMP

TE Part #2-1437012-4
609-006-1=HDW IDC JACKSOCKET A

TE Part #CQ53593001
C6A-24B134XN1FA-0CK9500

TE Part #CW1080-000
TXR40AZ00-2216BI

TE Part #7450793001
TR16-10-0

TE Part #EJ3570-000
TXR40AZ00-1607BI

TE Part #5-1616970-9
K200A1C=CONTACTOR 200 AMP
SPST 28 VDC

TE Part #CW1065-000
TXR40AZ00-1408BI

TE Part #CW9557-000
CBS-24CN21-21M-9

TE Part #CD61243001
44A0111-22-9CK0300

Documents

Product Drawings
322A012-25/225-0

English

Datasheets & Catalog Pages
1654025_Sec4_-25

English

Raychem Molded Parts Visual Guide

English

Solutions for Defense Applications Certified to VG Standards

English

Product Specifications
Product Specification

English