


COAXIAL SURGE PROTECTOR DEVICE, Slim Line GDT technology

3406.26.0004

Properties

- Slim in-line design
- Broadband operation from DC up to 5.8 GHz
- DC continuity for remote powering
- Permanently installed gas discharge tube
- RF power up to 60W max.

**Product configuration**

Main path connectors	Port 1: unprotected, TNC plug (male) Port 2: protected, TNC jack (female)
Mounting and grounding	MH4 (bulkhead mounting)

Material data

Housing material / plating	Brass / Silver / Gold Plating
Center contact, material / plating	Port 1: Brass / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Frequency frame	0 MHz to 5800 MHz
Return loss typical	18.5 dB
Insertion loss typical	0.2 dB
CW power frame	60 W

Electrical bands

	Range 1	Range 2
Frequency range	0 MHz ... 5600 MHz	5600 MHz ... 5800 MHz
Return loss	20 dB	18.5 dB
Insertion loss	0.2 dB	0.2 dB

Electrical remarks

Surge current handling capability	10 single / 5 multiple kA (test pulse 8/20 μ s)
Residual pulse energy	250 μ J typically (test pulse 4 kV 1.2/50 μ s / 2 kA 8/20 μ s) main path - protected side
Gas tube	Yes DC, GDT included, not replaceable

COAXIAL SURGE PROTECTOR DEVICE, Slim Line GDT technology

3406.26.0004

Mechanical data	
Weight	45 g
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 85°C
Storage temperature	-40 °C ... 85°C
Ingress protection (IP Rating)	IP20

Ordering Information Table	
Item number	Item description
23026102	3406.26.0004

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1969 / Date of publication: 07.11.2023 / uncontrolled copy