

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/gb/products/0813925>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X1. 2, THERMOMARK S1.1, mounting type: Assembly with cable ties, cable diameter: > 10 mm, Number of individual labels: 4000, text field height: 8 mm, text field width: 24 mm

Commercial data

Item number	0813925
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG2311
Product key	BG2311
GTIN	4017918958022
Weight per piece (including packing)	656.4 g
Weight per piece (excluding packing)	656.4 g
Customs tariff number	39191080
Country of origin	BE

KMT 24X10 WH 200 - Cable marker

0813925

<https://www.phoenixcontact.com/gb/products/0813925>



Technical data


Product properties

Product type	Conductor marking
Type	Roll

Marking

Number of individual labels	4000
Number of individual labels per row	4
Identification technology	Thermal transfer for rolls

Dimensions

Dimensional drawing	
Width	10 mm
Length	24 mm

External dimensions

Outside diameter	10 mm ... 136 mm
------------------	------------------

Text field

Text field width	24 mm
Text field height	8 mm

Material specifications

Color	white (RAL 9010)
Material	Polyester foil

Cable/line

External cable diameter	> 10.00 mm
-------------------------	------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/gb/products/0813925>

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-60 °C ... 120 °C
Recommended ambient temperature (storage/transport)	≤ 27 °C
Recommended humidity (storage/transport)	≤ 60 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/gb/products/0813925>

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------


KMT 24X10 WH 200 - Cable marker

0813925

<https://www.phoenixcontact.com/gb/products/0813925>



Drawings



KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/gb/products/0813925>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/gb/products/0813925>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk